

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

L-com's Exclusive Right Angle Category 5E Keystone Couplers

An exclusive product design from L-com, these new right angle Category 5E couplers offer true 90° connectivity and meet Category 5E standards. These unique right angle keystone couplers were designed to address tight fit applications commonly seen with wall plates and some patch panel designs. These robust right angle Cat 5E couplers fit standard .765" (0.3cm) X .585" (0.2cm) keystone openings and can be used for myriad voice, video and data applications.


Features of this right angle coupler:

- High Performance Cat 5E right angle coupler for panel, wall plate and enclosure mounting
- Gold plated contacts provide reliable connections with repeated mating cycles
- EIA568A/B dual wiring provides compatibility in every installation
- RJ45 jacks conform to TIA-1096
- Meets or exceeds Category 5E standards


RoHS Right Angle Category 5E Keystone Coupler

TDG1026KC-R5E	Category 5E Unshielded RJ45 (8x8) Right Angle Keystone Coupler	7.95	7.31	6.68	6.04	5.41
TDG1026KCS-R5E	Category 5E Shielded RJ45 (8x8) Right Angle Keystone Coupler	9.95	9.15	8.36	7.56	6.77

Exclusive





Exclusive



Using L-com's right angle Cat 5E coupler

The unique design of the L-com TDG1026KC-R5E right angle Cat5E coupler allows for cable connectivity in tight fit/confined space applications found with premise wiring installations involving wall plates and with MDF and IDF applications where patch panel depth is limited.



RoHS Premium Panel Mounted Modular Coupler Kits - Category 3, 5E and 6 - Shielded and Unshielded

These unique coupler kits allow panel mounting in virtually any panel thickness. A solid die-cast metal mounting frame provides secure mounting and reliable grounding. Kits include a snap-in coupler, mounting frame and two 4-40 machine screws.

ECF504-C3	Category 3 Unshielded RJ45 (8x8) Deluxe Panel Coupler Kit	4.45	4.09	3.74	3.38	3.03
ECF504-SC3	Category 3 Shielded RJ45 (8x8) Deluxe Panel Coupler Kit	6.95	6.39	5.84	5.28	4.73
ECF504-C5	Category 5E Unshielded RJ45 (8x8) Deluxe Panel Coupler Kit	6.95	6.39	5.84	5.28	4.73
ECF504-SC5E	Category 5E Shielded RJ45 (8x8) Deluxe Panel Coupler Kit	8.95	8.23	7.52	6.80	6.09
ECF504-C6	Category 6 Unshielded RJ45 (8x8) Deluxe Panel Coupler Kit	7.95	7.31	6.68	6.04	5.41
ECF504-SC6	Category 6 Shielded RJ45 (8x8) Deluxe Panel Coupler Kit	9.95	9.15	8.36	7.56	6.77

RoHS RJ45 (8x8) Keystone Feed-Thru Couplers - Shielded and Unshielded Category 3, 5E and 6

These couplers utilize two RJ45 (8x8) modular jacks and fit into a standard keystone style opening. A slim housing design permits high density mounting. Couplers listed include Category 3, Category 5E and Category 6 performance ratings in both shielded and unshielded versions. Connector housings enclosed within a fully stamped shielding. Designed to work with EIA/TIA 568A and B wiring.

TDG1026KC3	Category 3 Unshielded RJ45 (8x8) Keystone Feed-thru Coupler	2.25	2.07	1.89	1.71	1.53
TDG1026KS-8P	Category 3 Shielded RJ45 (8x8) Keystone Feed-thru Coupler	4.95	4.55	4.16	3.76	3.37
TDG1026KC5	Category 5E Unshielded RJ45 (8x8) Keystone Feed-thru Coupler	4.95	4.55	4.16	3.76	3.37
TDG1026KS-C5E	Category 5E Shielded RJ45 (8x8) Keystone Feed-thru Coupler	6.95	6.39	5.84	5.28	4.73
TDG1026KC6	Category 6 Unshielded RJ45 (8x8) Keystone Feed-thru Coupler	5.95	5.47	5.00	4.52	4.05
TDG1026KS-C6	Category 6 Shielded RJ45 (8x8) Keystone Feed-thru Coupler	7.95	7.31	6.68	6.04	5.41




Easily panel mount a keystone style connector

Keystone style refers to the snap-in mounting mechanism that many manufacturers have adopted.



Online Video

L-com.com/Videos/A10



RoHS Premium Keystone Style RJ45 (8x8) Feed-Thru Modular Couplers - Category 5E Rated

Two Category 5E feed-thru modular couplers for mating EIA568 A or B Category 5 connections. In both shielded and unshielded versions, this unique offset design maintains Category 5E performance and limits depth to only 1.25" (0.5cm). Designed to mate with keystone style holes. Color: Black or Silver.

UJ5T568	Modular Coupler, Cat. 5E RJ45 (8x8), Unshielded	Black	9.95	9.15	8.36	7.56	6.77
UJ5T568S	Modular Coupler, Cat. 5E RJ45 (8x8), Shielded	Silver	11.95	10.99	10.04	9.08	8.13



To see our entire product offering go to... L-com.com