

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Professional Grade Crimp and Compression Tools - for Professional Grade Type F Plugs

Two new ratchet action crimp tools are now offered. Sturdily constructed from high carbon steel ensures long life expectancy. Fully machined crimp cavities ensure accurate crimps every time.

HTS3162CT	Hex Crimp Tool .360" and .470" Sizes	66.50	62.51	58.52	54.53	CALL
HTS-EX	Compression Connector Crimp Tool	79.95	75.15	70.36	65.56	CALL

Easy Strip RG59/6 Coaxial Cable Stripper

A must for anyone working with coaxial cabling. This tool provides a precise industry standard 1/4" (0.6cm) cable prep for RG59 and 6 in seconds. Simply compress the jaw, place the cable into the strip insert, release then spin the tool 360° and you're ready to crimp.

HTS8700ES	CATV Stripper Tool for RG59/6	17.50	16.45	15.40	14.35	CALL
HTS8700RB	10 Replacement Cartridges for RG59/6	54.95	51.65	48.36	45.06	CALL

Type F Installation Kit - Toner, Crimper, Stripper and 40 Plugs for RG59 or RG6 Coaxial Cabling

We've assembled a kit for installers and technicians who want to terminate popular Type F coaxial cabling. Each kit includes 40 professional grade Type F plugs, a cable stripping tool, a connector crimping tool and a pocket toner. There are two kits to choose from, one for RG59 and one for RG6.

TCK59F	Type F Connector Installation Kit for RG59	99.95	93.95	87.96	81.96	75.96
TCK60F	Type F Connector Installation Kit for RG6	99.95	93.95	87.96	81.96	75.96

Rotary Coaxial Cable Strippers - Adjusted to Accurately Prepare Popular Coaxials

Time saving tools to quickly and accurately cut and trim the coaxial jacket, shield and inner insulation in one easy step. Compartment holds hex key to align sensitive socket and adjust blade cut for optimum results. Available in two or three blade configurations.

AT-STRIP-01	Coax Cable Stripper, 2-Blade for 100/174/200/240/316 Series	14.95	14.35	13.75	12.71	11.21
AT-STRIP-02	Coax Cable Stripper, 2-Blade for 100 Series, RG8/11/213/214	14.95	14.35	13.75	12.71	11.21
HT302B	Coax Cable Stripper, 2-Blade for RG58/59/62	14.95	13.75	12.56	11.36	10.17
HT3021	Set of 4 Replacement Blades for HT302	4.95	4.55	4.16	3.76	3.37
HT312A	Coax Cable Stripper, 3-Blade for RG59/62/6	19.95	18.35	16.76	15.16	13.57
HT312B	Coax Cable Stripper, 3-Blade for RG58/59/62	19.95	18.35	16.76	15.16	13.57
HT312S	Coax Cable Stripper, 3-Blade for RG213/11/8	19.95	18.35	16.76	15.16	13.57
HT312X	Coax Cable Stripper, 3-Blade for 3.5 to 5mm dia.	19.95	18.35	16.76	15.16	13.57
HT3121	Set of 4 Replacement Blades for HT312	4.95	4.55	4.16	3.76	3.37

Rotary Coaxial Cable Strippers for 400/600 Series

Quickly and accurately cut and trim the coaxial jacket, shield and inner insulation in two easy steps. Just insert the un-stripped end of the coax cable into the tool, spin clockwise 4 or 5 times, then insert into other end of tool, spin clockwise 4 or 5 times again and pull off the unwanted portion.

HT-STRIP400-1	Coax Cable Stripper for 400-Series Cable	54.99	52.79	50.59	46.74	41.24
HT-STRIP600-1	Coax Cable Stripper for 600-Series Cable	54.99	52.79	50.59	46.74	41.24
HT-STRIP-B1	Replacement Blades for HT-STRIP400-1/HT-STRIP600-1	7.20	6.91	6.62	6.12	5.40

USA Made Crimping Tool Accepts Dies for Coaxial or Modular Type Terminations

The HTS2100 crimp tool accepts a variety of dies that allow it to crimp modular or coaxial terminations. This top of the line tool is more compact than competitors' models allowing easier crimping ability for people with smaller hands. Molded grips and carbon steel frame is conservatively rated at 50,000+ crimps. This tool also accepts modular die sets listed on page 63.

HTS2100	Crimp Tool Body, accepts any HTS2100 Die Set	59.95	58.75	57.55	56.35	55.15
HTS2100-51	RG58 / RG59 Die Set, use for BNCs and TNCs, .068, .213 and .255 hex	36.00	33.84	31.68	29.52	CALL
HTS2100-53	RG58 / RG59 Die Set, use for SMA's, .042 square, .213 and .255 hex	36.00	33.84	31.68	29.52	CALL
HTS2100-54	RG58 / RG59 Plenum Die Set, use for Plenum BNCs, .068, .190 & .213 hex	36.00	33.84	31.68	29.52	CALL
HTS2100-60	RG174 Die Set, use for BNCs and SMA's, .068 and .178 hex	36.00	33.84	31.68	29.52	CALL

Weatherproofing Tape

HT-TAPE01	3M® Self-Healing Weatherproofing Tape	20.99	19.94	18.89	17.84	CALL
HT-TAPE104	COAX-SEAL #104 Hand Moldable Plastic Weatherproofing Tape	3.29	3.16	3.03	2.80	2.47

Item #	Description	List Price
--------	-------------	------------

Gale Pocket Toner® NX1

Test for continuity and short circuits on coaxial cables in one easy step. Basic professional coaxial testing does not get any more compact and simple as PTNX1. This is the new NX version of the classic black Pocket Toner® first invented by Gale Corporation years ago. This new NX version features lightweight aluminum construction, a standard AAA battery, and new dual buzzers that audibly indicate continuity at both ends of the test cable. Like all Pocket Toner® NX test tools, the NX1 is now 100% low voltage protected so connecting it to live low voltage systems will not damage the tool.

PTNX1	Gale Pocket Toner® NX1	29.95
-------	------------------------	-------

Gale Pocket Toner® NX2

The individual PTNX2 is for the technician that works primarily with coaxial cable that wants a powerful but super-compact tool to fit in his or her pocket. In addition to testing for continuity and short circuits PTNX2 is packed with advanced features like indication of AC or DC voltage, 50-75 Ohm terminators and auto shut-off to conserve battery life. PTNX2 instantly displays all test results on an easy to read 8-segment LED display as well as giving audible feedback at both ends of the test cable. Like all Pocket Toner® NX test tools, the NX2 is now 100% low voltage protected so connecting it to live low voltage systems will not damage the tool.

PTNX2	Gale Pocket Toner® NX2	39.95
-------	------------------------	-------

Professional Grade 8 Point Center Pin Crimp Tool

This professional grade tool makes pin crimping a breeze. Featuring a multipoint design which has proven to be one of the most reliable attachment methods. Designed for use with the BAC-UPL Series plugs.

HT010-0055	8 Point Center Pin Crimp Tool	182.40
------------	-------------------------------	--------

HTS-CT4L Professional Crimp Tool Accepts Dies for Coaxial Hex Dies

An ergonomic design makes this a tool of choice for professionals. A comfortable, high leverage handle minimizes fatigue. A precision ratchet mechanism assures full cycle crimping. Dies can be easily interchanged with a phillips or flat blade screwdriver.

HTS-CT4L	Professional Crimp Tool Frame	135.00
HTS-CD3-11	734/735 Hex Crimp Die (.255", .178")	95.50
HTS-CD3-21	1505/1506 Hex Crimp Die (.255", .290")	135.00



Helpful videos

How-to videos help with some of today's popular product applications. L-com.com/Tips