

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

RoHS Protective Covers for Plugs and Jacks - Protect Unused Ports and Cables from Contact Damage

These covers are perfect for protecting unused ports in wall plates and expensive equipment from physical damage, dirt and grime. Made from flexible PVC, these covers attach easily and stay in place with a snug friction fit.

MP45P	RJ45 Protective Covers for Plugs, Pkg/100	14.95	14.65	14.35	14.05	13.75
MP45J	RJ45 Protective Covers for Jacks, Pkg/100	15.95	15.63	15.31	14.99	14.67

DSL Line Conditioners - Filters Noise for Better Performance

These are two types of DSL Line Conditioners for filtering out unwanted noise. The devices use 2 pole low pass filters. Inline plug/jack or wall plate configurations. Color: Ivory. Specifications: REN 0.2B; DC Resistance Through T&R to Phone: 10 Ohms; Loading Capacity: 47nF; Attenuation Distortion ± 1 dB max.; 3 dB Cutoff Point.

S900LCC50-I	Inline DSL Conditioner, RJ12 (6x6) Male / Female	6.95	6.67	6.39	6.12	5.84
S630LCC-I	Wall Mount DSL Conditioner, RJ12 (6x6) Jack	7.95	7.63	7.31	7.00	6.68

RoHS Wire Tap and Butt Splice - Gel Filled IDC Connectors

These handy IDC connectors make wire splicing a snap. Gel filled IDC contact area provides a moisture resistant barrier for reliable connections. Usable with 19-26 AWG copper wire with a .066" maximum insulation diameter (.060 max. for WT-UY). Sold in 100 piece packs.

WT-UY	UY Butt Splice 2 Wire Connector, Gel Filled, Pkg/100	9.95	9.55	9.15	8.76	8.36
WT-UR	UR Butt Splice, 3 Wire Connector, Gel Filled, Pkg/100	12.95	12.43	11.91	11.40	10.88
WT-UB	UB Butt Tap Connector, Gel Filled, Pkg/100	12.95	12.43	11.91	11.40	10.88



110 Wiring Block Field Termination Kits - Everything Necessary to Wire a 110 Block

Each kit contains one 100 pair wiring block with detachable legs, label holders with designation labels and sufficient connecting blocks. Note: Each kit includes enough connecting blocks to complete each 25 pair termination strip on the 110 wiring block. (ex. The S110K-4PR kit would include five four pair and one five pair connecting block per 25 pair termination strip).

Wiring blocks are the main instrument in setting up horizontal wiring in a 110 style connector system. These are surface mountable molded plastic units that secure and organize cable pairs. Designation strips are mounted to the wiring block addressing each cable termination. 2, 3, 4 or 5 pair connecting blocks snap over the wire terminations on the wiring block. These contain insulation displacement quick connect clips and provide a gas tight connection between the cable conductor and cross connect system.

S110K-3PR	100 Pair Wiring Block Kit with 3 Pair Connecting Blocks	39.95	39.15	38.35	37.55	36.75
S110K-4PR	100 Pair Wiring Block Kit with 4 Pair Connecting Blocks	41.95	41.11	40.27	39.43	38.59
S110K-5PR	100 Pair Wiring Block Kit with 5 Pair Connecting Blocks	44.95	44.05	43.15	42.25	41.35

50 Pair 66 Style Category 5 Block

This 66 style 50 pair block has been designed to meet Category 5 requirements as specified by the EIA/TIA. Ease of use and low cost has made this style of block one of the most popular termination methods. Improved design now permits use in data applications up to 100 Mbps! Included are 100 quick connect bridging clips and a clear protective cover. 66 type tool required for termination.

S66M1-50-C5	50 Pair 66 Style Block, Category 5 Rated	16.95	16.61	16.27	15.93	15.59
C1127-A1	Bridging Clips for 66 Style Blocks, Pkg/50	4.99	4.79	4.59	4.39	CALL

RoHS Multi-Pair Termination Tool for 110 Blocks

This professional grade tool is designed to terminate and cut up to 5 pairs of UTP wires once they are laid into the 110 connector. Blade is reversible with one side crimping and cutting excess wire and the other side just crimping. Impact mechanism makes reliable terminations every time.

S110MPIC	Multi Pair Impact Tool for 110 Blocks	149.95	143.95	137.95	131.96	CALL
--------------------------	---------------------------------------	--------	--------	--------	--------	------

Professional Grade Cable Splicer Knife, Scissor and Kit

These tools are a great addition to any cable technicians tool kit. The CS925 is an industrial grade serrated scissor capable of cutting thin wires and cable jacketing. This tool also has wire stripping notches on one blade as well as a scraper and file on the back of the other. The CK6 is a forged steel splicer knife with red cushioned handle. It comes in handy whenever a sharp blade is necessary. The CS925KIT offers both tools plus a heavy duty leather holder that will keep the knife and scissor secured to a tool belt.

CS925	Cable Splicer Serrated Scissor	16.50	15.84	15.18	14.52	CALL
CK6	Cable Splicer Knife	10.90	10.46	10.03	9.59	CALL
CS925KIT	Knife and Scissor with Holder	33.50	32.16	30.82	29.48	CALL

Parallel Action Pliers - Use for Compressing IDC Body to Jack

These parallel action pliers are great for crimping wire taps and butt splices. The jaws of the tool work close in parallel providing a better crimp than regular pliers.

HT1008	Parallel Action Pliers	49.95	48.95	47.95	46.95	45.95
------------------------	------------------------	-------	-------	-------	-------	-------

RoHS Premium Auto Impact Tool - Our Best Model, Features an Adjustable Spring Load

Now installers can make effortless, uniform connections with L-com's premium auto impact tool. Set tool for high or low impact with a variable impact pressure control that will provide the right amount of force. Blades are easily reversible, one end terminates only while the other terminates and cuts. This model features a hidden storage compartment which opens to fit an extra blade. Accepts blades for 66, 110 and Krone use. This tool comes without blades, order separately.

H351	Premium Impact Tool Body Only, Without Blade	38.50	36.96	35.42	33.88	32.34
----------------------	--	-------	-------	-------	-------	-------

RoHS Reversible Blades - Fit H351 Series Tool

H351B66	Impact Blade, Reversible for 66 Terminals	9.95	9.55	9.15	8.76	8.36
H351B110	Impact Blade, Reversible for 110 Terminals	9.95	9.55	9.15	8.76	8.36
H351B-K	Impact Blade, Reversible for Krone Terminals	9.95	9.55	9.15	8.76	8.36

Note: Mixing of blades is allowed for quantity pricing



"I am currently working on a project that uses at least 6 of L-com's connectors and panels. I consider your web site & component data/solid model availability to be superior to any other site. Your CAD step files are really well done and the solid models are priceless." - Phil Marsh, M.E. Solutions, Product Design & Engineering Services