

Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------


**✓RoHS RJ45 (8x8) Keystone Feed-Thru Couplers - Shielded and Unshielded Category 3, 5E and 6**

These couplers utilize two RJ45 (8x8) modular jacks and fit into a standard keystone style opening. A slim housing design permits high density mounting. Couplers listed include Category 3, Category 5E and Category 6 performance ratings in both shielded and unshielded versions. Connector housings enclosed within a fully stamped shielding. Designed to work with EIA/TIA 568A and B wiring.


<a href="#">TDG1026KC3</a>	Category 3 Unshielded RJ45 (8x8) Keystone Feed-thru Coupler		3.99	3.59	3.19	2.79	2.39
<a href="#">TDG1026KS-8P</a>	Category 3 Shielded RJ45 (8x8) Keystone Feed-thru Coupler		8.95	8.06	7.16	6.27	5.37
<a href="#">TDG1026KC5</a>	Category 5E Unshielded RJ45 (8x8) Keystone Feed-thru Coupler		8.95	8.06	7.16	6.27	5.37
<a href="#">TDG1026KS-C5E</a>	Category 5E Shielded RJ45 (8x8) Keystone Feed-thru Coupler		10.95	9.86	8.76	7.67	6.57
<a href="#">TDG1026KC6</a>	Category 6 Unshielded RJ45 (8x8) Keystone Feed-thru Coupler		9.95	8.96	7.96	6.97	5.97
<a href="#">TDG1026KS-C6</a>	Category 6 Shielded RJ45 (8x8) Keystone Feed-thru Coupler		12.95	11.66	10.36	9.07	7.77

**Easily panel mount a keystone style connector**


Keystone style refers to the snap-in mounting mechanism that many manufacturers have adopted.



Align connector in proper orientation to the opening.



Seat bottom retainer and pivot connector upward while depressing upper retainer.



Connector fully seated.




[www.l-com.com/Videos/A10](http://www.l-com.com/Videos/A10)

**✓RoHS Premium Keystone Style RJ45 (8x8) Feed-Thru Modular Couplers - Category 5E Rated**

Two Category 5E feed-thru modular couplers for mating EIA568 A or B Category 5 connections. In both shielded and unshielded versions, this unique offset design maintains Category 5E performance and limits depth to only 1.25". Designed to mate with keystone style holes. Color: Black or Silver.

<a href="#">UJ5T568</a>	Modular Coupler, Cat. 5E RJ45 (8x8), Unshielded	Black	9.95	9.15	8.36	7.56	6.77
<a href="#">UJ5T568S</a>	Modular Coupler, Cat. 5E RJ45 (8x8), Shielded	Silver	11.95	10.99	10.04	9.08	8.13



**✓RoHS Premium Keystone Style - 16 and 32 Port Feed-Thru Modular Panels, Category 5E Rated**

These 19" rack panels utilize the UJ5T568 and UJ5T568S couplers. 16 and 32 port versions available in shielded and unshielded configurations. Category 5E rated. Color: Black.

<a href="#">PR175UT568</a>	1.75" 16 Port Cat. 5E Feed-Thru Panel, Unshielded	Black	179.95	165.55	151.16	136.76	CALL
<a href="#">PR175UT568S</a>	1.75" 16 Port Cat. 5E Feed-Thru Panel, Shielded	Black	199.95	183.95	167.96	151.96	CALL
<a href="#">PR35UT568</a>	3.50" 32 Port Cat. 5E Feed-Thru Panel, Unshielded	Black	299.95	275.95	251.96	227.96	CALL
<a href="#">PR35UT568S</a>	3.50" 32 Port Cat. 5E Feed-Thru Panel, Shielded	Black	379.95	349.55	319.16	288.76	CALL


**✓RoHS Keystone Style - 16 and 32 Port Feed-Thru Modular Panels - Category 6 Rated**

These rack panels utilize the TDG1026KC6 or TDG1026KS-C6 Category 6 couplers. 16 and 32 port versions are available in shielded and unshielded configurations. Color: Black.

<a href="#">PR175C6-16</a>	1.75" 16 Port Cat. 6 Feed-Thru Panel, Unshielded	Black	189.95	174.75	159.56	144.36	CALL
<a href="#">PR175C6-16S</a>	1.75" 16 Port Cat. 6 Feed-Thru Panel, Shielded	Black	239.95	220.75	201.56	182.36	CALL
<a href="#">PR35C6-32</a>	3.50" 32 Port Cat. 6 Feed-Thru Panel, Unshielded	Black	319.95	294.35	268.76	243.16	CALL
<a href="#">PR35C6-32S</a>	3.50" 32 Port Cat. 6 Feed-Thru Panel, Shielded	Black	369.95	340.35	310.76	281.16	CALL

**How Rack Spaces and Sizes are Measured**

Racks are a great way to neaten up wiring closets and labs. Network equipment and rack panels usually come in 1.75", 3.5" and 5.25" heights. (1, 2 and 3 rack spaces).



**Best Seller**

**TDG1026K PANEL OPENING**

0.765 (19.3)  
0.585 (14.9)

**UJ5T568 (Unshielded)**  
**UJ5T568S (Shielded)**

Network Rating: Category 5E  
Color: Black or Silver  
Gold Plating: 50 microinches  
Flammability Rating: 94V-0

**PR175UT568**  
**PR35UT568**  
**PR175C6-16**  
**PR35C6-32**

**How to terminate a keystone style connector**  
See the free video tip and more at [L-com.com/Videos/A10](http://L-com.com/Videos/A10)