

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

**DVI Products**

DVI (Digital Video Interface) is a widely used interface specifically designed for the transmission of digital signals. Our DVI cable assemblies and adapters are offered in various interface combinations and gender configurations to address a broad range of connection applications.

**DVI Cable Assemblies - Fully Molded with Ferrites**

This series of DVI cable assemblies features a molded integrated ferrite on both ends for EMI/RFI protection and a fully molded and shielded backshell. Offered in 4 standard lengths not exceeding the recommended 5 meter maximum for DVI cables.

**✓RoHS DVI-I Single Link Cable Assembly with Ferrites**

<a href="#">CTLDVI-ISL-MM-3</a>	DVI Cable, DVI-I Single Link Male / Male, 3.0 ft	35.00	32.20	29.40	26.60	23.80
<a href="#">CTLDVI-ISL-MM-5</a>	DVI Cable, DVI-I Single Link Male / Male, 5.0 ft	40.00	36.80	33.60	30.40	27.20
<a href="#">CTLDVI-ISL-MM-10</a>	DVI Cable, DVI-I Single Link Male / Male, 10.0 ft	52.50	48.30	44.10	39.90	35.70
<a href="#">CTLDVI-ISL-MM-15</a>	DVI Cable, DVI-I Single Link Male / Male, 15.0 ft	65.00	59.80	54.60	49.40	44.20

**✓RoHS DVI-I Dual Link Cable Assembly with Ferrites**

<a href="#">CTLDVI-I-MM-3</a>	DVI Cable, DVI-I Dual Link Male / Male, 3.0 ft	40.00	36.80	33.60	30.40	27.20
<a href="#">CTLDVI-I-MM-5</a>	DVI Cable, DVI-I Dual Link Male / Male, 5.0 ft	45.00	41.40	37.80	34.20	30.60
<a href="#">CTLDVI-I-MM-10</a>	DVI Cable, DVI-I Dual Link Male / Male, 10.0 ft	57.50	52.90	48.30	43.70	39.10
<a href="#">CTLDVI-I-MM-15</a>	DVI Cable, DVI-I Dual Link Male / Male, 15.0 ft	70.00	64.40	58.80	53.20	47.60

**✓RoHS DVI-D Single Link Cable Assembly with Ferrites**

<a href="#">CTLDVIMM-3</a>	DVI Cable, DVI-D Single Link Male / Male, 3.0 ft	30.00	27.60	25.20	22.80	20.40
<a href="#">CTLDVIMM-5</a>	DVI Cable, DVI-D Single Link Male / Male, 5.0 ft	35.00	32.20	29.40	26.60	23.80
<a href="#">CTLDVIMM-10</a>	DVI Cable, DVI-D Single Link Male / Male, 10.0 ft	47.50	43.70	39.90	36.10	32.30
<a href="#">CTLDVIMM-15</a>	DVI Cable, DVI-D Single Link Male / Male, 15.0 ft	60.00	55.20	50.40	45.60	40.80

**✓RoHS DVI-D Dual Link Cable Assembly with Ferrites**

<a href="#">CTLDVI-DL-MM-3</a>	DVI Cable, DVI-D Dual Link Male / Male, 3.0 ft	35.00	32.20	29.40	26.60	23.80
<a href="#">CTLDVI-DL-MM-5</a>	DVI Cable, DVI-D Dual Link Male / Male, 5.0 ft	40.00	36.80	33.60	30.40	27.20
<a href="#">CTLDVI-DL-MM-10</a>	DVI Cable, DVI-D Dual Link Male / Male, 10.0 ft	52.50	48.30	44.10	39.90	35.70
<a href="#">CTLDVI-DL-MM-15</a>	DVI Cable, DVI-D Dual Link Male / Male, 15.0 ft	65.00	59.80	54.60	49.40	44.20

**DVI Adapter Cables - Adapt from DVI to HD15 and DFP**

This series of cable assemblies allows adaptation from DVI to compatible HD15 and DFP interfaces.

**✓RoHS DVI-A to HD15 Cable Assembly with Ferrites**

<a href="#">CTLDVI-HD-MM-3</a>	DVI Cable, DVI-A to HD15 Male / Male, 3.0 ft	25.00	23.00	21.00	19.00	17.00
<a href="#">CTLDVI-HD-MM-5</a>	DVI Cable, DVI-A to HD15 Male / Male, 5.0 ft	26.50	24.38	22.26	20.14	18.02
<a href="#">CTLDVI-HD-MM-10</a>	DVI Cable, DVI-A to HD15 Male / Male, 10.0 ft	30.25	27.83	25.41	22.99	20.57
<a href="#">CTLDVI-HD-MM-15</a>	DVI Cable, DVI-A to HD15 Male / Male, 15.0 ft	34.00	31.28	28.56	25.84	23.12

**✓RoHS DVI-D to DFP Cable Assembly with Ferrites**


<a href="#">CTLDVIMR-3</a>	DVI Cable, DVI-D to DFP Male / Male, 3.0 ft	20.00	18.40	16.80	15.20	13.60
<a href="#">CTLDVIMR-5</a>	DVI Cable, DVI-D to DFP Male / Male, 5.0 ft	21.50	19.78	18.06	16.34	14.62
<a href="#">CTLDVIMR-10</a>	DVI Cable, DVI-D to DFP Male / Male, 10.0 ft	25.25	23.23	21.21	19.19	17.17
<a href="#">CTLDVIMR-15</a>	DVI Cable, DVI-D to DFP Male / Male, 15.0 ft	29.00	26.68	24.36	22.04	19.72

**DVI KVM (Keyboard, Video, Mouse) Cables - Mini DIN 6 Connectors**

This series of KVM cables is offered transitioning the video from DVI to HD15. Both male to male and male to female configurations are available.


**✓RoHS DVI / HD15 KVM Cable Assembly Combine DVI-A with HD15 + 2 Mini DIN 6 Connectors**

<a href="#">CTLDVIKVM-2</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6 Male / Male, 2.0m	40.00	36.80	33.60	30.40	27.20
<a href="#">CTLDVIKVM-3</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6 Male / Male, 3.0m	45.00	41.40	37.80	34.20	30.60
<a href="#">CTLDVIKVM-5</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6 Male / Male, 5.0m	55.00	50.60	46.20	41.80	37.40
<a href="#">CTLDVIKVMF-2</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6 Male / Female, 2.0m	40.00	36.80	33.60	30.40	27.20
<a href="#">CTLDVIKVMF-3</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6 Male / Female, 3.0m	45.00	41.40	37.80	34.20	30.60
<a href="#">CTLDVIKVMF-5</a>	DVI KVM Cable, DVI-A to HD15 + 2 Mini DIN 6 Male / Female, 5.0m	55.00	50.60	46.20	41.80	37.40



**Did you know...**

DVI-A cables can be used with DVI-I interfaces/cables?



Tip

*What is the difference between DVI Single Link and Dual Link?*

DVI dual link, as the name implies, has more conductors than the DVI single link for transmitting signal. Single link DVI supports a maximum bandwidth of 165 MHz (1920 x 1080 at 60 Hz, 1280 x 1024 at 85 Hz) and utilizes 18 of the 24 available pins. Dual link DVI utilizes all 24 available pins and supports 2x 165 MHz maximum bandwidth (2048 x 1536 at 60 Hz, 1920 x 1080 at 85 Hz).

DVI Single Link

DVI Dual Link

**Same day shipping**  
 Orders placed before 4:00 EST ship the same day.