

APC Personal SurgeArrest 8 Outlet

The APC-PER8T Personal SurgeArrest 8 Outlet system provides reliable surge protection for home or office computers and electronic equipment. The PER8T features a right angle power plug and transformer block spacing. Includes a limited lifetime manufacturer's warranty.

Item #	Capacity (VA/Watts)	System Type	Number of Outlets	Backup Time Half/Full Load	Dimensions (Inches)	Shipping Weight	Price
APC-PER8T	N/A	Surge Only	8	N/A	8w x 1.75h x 5.75d	3.0	20.95

Tripp Lite Internet Office Series Power Back-up System

Tripp Lite's Internet Office standby UPS systems offer complete protection from blackouts, brownouts and transient surges on both AC and dialup modem lines. The Internet Office offers complete power protection in an ultra-compact, flat-pack housing. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. A built-in single line RJ11 phone suppression jacks protect modem, fax machine, cordless phone or other peripheral with standard dialup phone connection.

Item #	Capacity (VA/Watts)	System Type	Number of Outlets	Backup Time Half/Full Load	Dimensions (Inches)	Shipping Weight	Price
TL-OFFICE300	300/150	Line Interactive	6	10/4 min	2.6w x 11h x 4.5d	5.0	75.00
TL-OFFICE500	500/280	Line Interactive	6	5/17 min	4.75w x 8.25h x 7d	16.0	119.00

Tripp Lite BCPRO Series Desktop UPS Systems

Tripp Lite's BCPRO600 standby UPS system offers surge suppression and long lasting battery support for personal computers, internet working equipment and other sensitive electronics. Internal UPS circuits support entry level PC systems for up to 45 minutes during power failures and brownouts so that connected equipment can be shutdown without data loss. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure, USB cable included.

Item #	Capacity (VA/Watts)	System Type	Number of Outlets	Backup Time Half/Full Load	Dimensions (Inches)	Shipping Weight	Price
TL-BCPRO600	600/345	Line Interactive	6	19/7 min	5.25w x 10.75h x 7.25d	19.0	139.00
TL-BCPRO1050	1050/705	Line Interactive	6	23/7 min	7.25w x 11.75h x 7.25d	28.6	369.00
TL-BCPRO1400	1400/940	Line Interactive	6	24/8 min	7.25w x 12.75h x 9d	36.4	529.00

Tripp Lite Smart Pro® Intelligent UPS System

The Tripp Lite Smart Pro® Intelligent UPS System is an ideal power protection solution for hubs, routers, switches, telephone systems and other critical moderate power devices. Innovative design packs battery backup and automatic voltage protection into an ultra small rack mountable package only a single rack space (1.75") high. Unattended shutdown capable via an RS232 port (PowerAlert® software included). The battery replacement door is conveniently located on the front panel. Shipping weight is 18.5 lb. Two-year manufacturer's warranty.

Item #	Capacity (VA/Watts)	System Type	Number of Outlets	Backup Time Half/Full Load	Dimensions (Inches)	Rack Mounting	Shipping Weight	Price
TL-SMART500RT1U	500/300	Line Interactive	7	17/5 min	17.5w x 1.75h x 11.75d	1 Space	18.8	195.00

Tripp Lite SmartOnline UPS Series

Tripp Lite's SmartOnline UPS Systems provide the highest level of power protection for mission-critical applications. True on-line operation completely isolates connected equipment from all power problems: blackouts, brownouts, surges, line noise, even harmonic distortion. Double-conversion operation continually converts incoming AC power into DC power, and then resynthesizes it back into normal AC power.

Item #	Capacity (VA/Watts)	System Type	Number of Outlets	Backup Time Half/Full Load	Dimensions (Inches)	Rack Mounting	Shipping Weight	Price
TL-SU750XL	750/600	Line Interactive	6	11/4 min	6.75w x 10h x 13.25d	No	28.7	479.00
TL-SU750RTLX2U	750/600	Line Interactive	6	11/4 min	17.5w x 3.5h x 13.5d	2 Space	29.0	529.00
SU1500RTLX2UA	1570/1200	Line Interactive	6	17/5 min	17.5w x 3.5h x 19d	2 Space	44.1	799.00
SU2200RTLX2UA	2200/1600	Line Interactive	6	18/5 min	17.5w x 3.5h x 19d	2 Space	47.4	1229.00
SU3000RTXR3U	3000/2400	Line Interactive	9	33/14 min	17.75w x 5.25h x 26d	3 Space	111.33	1949.00
SU5000RT4U	5000/3800	Line Interactive	12	17/8 min	17.5w x 7h x 30.75d	4 Space	149.6	3359.00

APC Smart-UPS Power Backup System

APC's Smart-UPS Power Backup System protects your data by supplying network-grade battery backup when power fails. The Smart-UPS series offers full time EMI/RFI filters preventing line noise from causing data errors. With PowerChute® software the uninterruptible power supply (UPS) will safely store data and shut down the network operating system before the battery is fully discharged. The product automatically performs a self-test every two weeks. This will alert users of degraded batteries before they wear out. Using wither the software, or the push of a button, users may perform self-tests anytime. Includes a limited lifetime manufacturer's warranty.

Item #	Capacity (VA/Watts)	System Type	Number of Outlets	Backup Time Half/Full Load	Dimensions (Inches)	Rack Mounting	Shipping Weight	Price
APC-SC420	420/260	Line Interactive	4	13.5/5.5 min	4.7w x 6.6h x 14.5d	N/A	22.0	139.00
SMT2200RM2U	2200/1980	Line Interactive	8	15.7/5.2 min	19w x 3.5h x 26d	2 Space	125.0	1125.00

Custom design and manufacturing capabilities

Our product design process takes you from concept to production. L-com.com/Custom

