



HG2424G  
CODE  
A



HG2427G  
CODE  
A



HG2430G  
CODE  
B



HG915G-NF  
CODE  
A



HG5421G (Vertical)  
CODE  
A

HG5421G  
(Horizontal)

Item #	Code	Description
--------	------	-------------

**2.4 GHz Grid Antennas**


L-com's HyperGain® high performance reflector grid Wi-Fi antennas are available in gain ranges of 15 dBi to 30 dBi and are ideally suited for long-range highly directional applications. These applications include point to point systems, point to multipoint systems and wireless bridges in the 2.4 GHz ISM band as well as IEEE 802.11b/g/n wireless LAN systems. L-com's grid antennas can be installed for either vertical or horizontal polarization. Not all models are available in 5 packs.

- Wide range of frequencies
- Extensive selection of gain choices
- Point-to-point systems
- Point-to-multipoint systems
- Long-range directional applications
- RoHS compliant

SOLD INDIVIDUALLY (NO 5-PACKS)			1-9	10-24	25-99	100-249	250-499
<a href="#">HG2415G-NM</a>	A	15dBi, 12in Pigtail with NM Connector	49.99	48.49	46.99	45.49	43.99
<a href="#">HG2427G</a>	A	27dBi, Integral NF Connector	249.99	229.99	209.99	189.99	169.99
<a href="#">HG2430G</a>	B	30dBi, 18in Pigtail with NF Connector	429.99	412.79	395.59	365.49	322.49
<a href="#">HG2430G-NM</a>	B	30dBi, 18in Pigtail with NM Connector	479.99	451.19	422.39	393.59	364.79
SOLD INDIVIDUALLY			1-4	5-9	10-24	25+	
<a href="#">HG2415G-NF</a>	A	15dBi, 12in Pigtail with NF Connector	34.99	34.64	34.29	33.94	
<a href="#">HG2419G-NF</a>	A	19dBi, 12in Pigtail with NF Connector	40.99	40.58	40.17	39.76	
<a href="#">HG2424G-NF</a>	A	24dBi, 12in Pigtail with NF Connector	54.99	54.44	53.89	53.34	
<a href="#">HG2424G-NM</a>	A	24dBi, 12in Pigtail with NM Connector	59.99	59.39	58.79	58.19	
5-PACKS			1-4	5-9	10-24	25+	
<a href="#">HG2415G-NF-5PK</a>	A	15dBi, 12in Pigtail with NF Connector, 5-Pack	159.99	158.39	156.79	155.19	
<a href="#">HG2419G-NF-5PK</a>	A	19dBi, 12in Pigtail with NF Connector, 5-Pack	197.99	192.05	186.11	180.17	
<a href="#">HG2424G-NF-5PK</a>	A	24dBi, 12in Pigtail with NF Connector, 5-Pack	249.99	237.49	224.99	212.49	
<a href="#">HG2424G-NM-5PK</a>	A	24dBi, 12in Pigtail with NM Connector, 5-Pack	259.99	246.99	233.99	220.99	

**Tip Tilt and Swivel Mounting**

The HG2430G antenna is supplied with a 60 degree tilt and swivel mast mount kit. This allows installation at various degrees of incline for easy alignment. Antenna alignment is critical to the system's operation between sites. This versatile mount aids the installer in the field to achieve better alignment accuracy, optimizing system performance for the user.



**900 MHz, 5.4 GHz and 5.8 GHz Grid Antennas**

L-com's HyperLink Brand grid antennas feature a multi-piece reflector grid. With this type of design they are not only easy to assemble, but it significantly reduces shipping costs compared to similar antennas with one piece reflector grid. All of our reflector grids are UV powder coated for durability and aesthetics and the open-frame design minimizes wind loading. Not all models are available in 5 packs.

- Superior performance
- Die cast aluminum construction
- All weather operation
- UV stable light gray powder coat finish
- 19° beam-width
- RoHS compliant

**RoHS 900 MHz Grid Antennas**

SOLD INDIVIDUALLY (NO 5-PACKS)			1-4	5-9	10-24	25+
<a href="#">HG918G-NF-2</a>	B	18dBi, 18in Pigtail with NF Connector	327.99	314.87	301.75	288.63
SOLD INDIVIDUALLY			1-4	5-9	10-24	25+
<a href="#">HG915G-NF</a>	A	15dBi, 30in Pigtail with NF Connector	70.99	70.28	69.57	68.86
5-PACKS			1-4	5-9	10-24	25+
<a href="#">HG915G-NF-5PK</a>	A	15dBi, 30in Pigtail with NF Connector, 5-Pack	329.99	320.09	310.19	300.29

**RoHS 5.4 GHz Grid Antennas**

SOLD INDIVIDUALLY			1-4	5-9	10-24	25+
<a href="#">HG5421G</a>	A	21dBi, Integral NF Connector	49.99	49.49	48.99	48.49
<a href="#">HG5426G</a>	A	26dBi, Integral NF Connector	53.99	53.45	52.91	52.37
5-PACKS			1-4	5-9	10-24	25+
<a href="#">HG5421G-5PK</a>	A	21dBi, Integral NF Connector, 5-Pack	239.99	232.79	225.59	218.39
<a href="#">HG5426G-5PK</a>	A	26dBi, Integral NF Connector, 5-Pack	259.99	252.19	244.39	236.59

**RoHS 5.8 GHz Grid Antennas**

SOLD INDIVIDUALLY			1-4	5-9	10-24	25+
<a href="#">HG5822G</a>	A	22dBi, Integral NF Connector	49.99	49.49	48.99	48.49
<a href="#">HG5827G</a>	A	27dBi, Integral NF Connector	53.99	53.45	52.91	52.37
5-PACKS			1-4	5-9	10-24	25+
<a href="#">HG5822G-5PK</a>	A	22dBi, Integral NF Connector, 5-Pack	239.99	227.99	215.99	203.99
<a href="#">HG5827G-5PK</a>	A	27dBi, Integral NF Connector, 5-Pack	259.99	252.19	244.39	236.59

**Tip Antenna Construction**

Two-piece grid antenna reflectors allow easy handling, shipping, and transportation to the site. These large grid antennas come in two symmetrical sections. They are bolted together on site easily, with the feed then installed. The antenna then is ready to be mounted in place on its mounting bracket (a number of brackets are available on the web site) to complete the installation.

