


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                 |         |           |
|-----------|-----------------|---------|-----------|
| REV       | DESCRIPTION     | DATE    | APPROVED  |
| A         | INITIAL RELEASE | 9/27/10 | D.GRIFFIN |
|           |                 |         |           |
|           |                 |         |           |



| LENGTH CODE CHART      |                              |                           |
|------------------------|------------------------------|---------------------------|
| CABLE# & LENGTH        | LENGTH SYMBOL                | EXAMPLES OF PART# USED    |
| CA-085FNMMN <u>XXX</u> | WHERE XXX = LENGTH IN INCHES | CA-085FNMMN16 (16 INCHES) |

NOTES:

ELECTRICAL:  
 IMPEDANCE: 50 OHM  
 FREQUENCY RANGE: 0 - 18 GHz

MISCELLANEOUS:  
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

|   |   |                                       |   |  |                          |                                |
|---|---|---------------------------------------|---|--|--------------------------|--------------------------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +3% / -0%<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ±.2<br>.XX = ±.02<br>.XXX = ±.005 | APPROVALS<br>DRAWN BY<br>D.FRISIELLO<br>CHECKED BY<br>K.BURGNER<br>APPROVED BY<br>K.BURGNER | DATE<br>9/24/10<br>9/24/10<br>9/24/10 |   | 45 BEECHWOOD DRIVE<br>NORTH ANDOVER, MA<br>01845 |                          |                                |
|   | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY                              | CATEGORY<br><b>COAXIAL</b>            | PRODUCT DESCRIPTION<br><b>CA TYPE N M/M .085 FORMABLE</b> | SIZE<br><b>A</b>                                 | FSCM NO.<br><b>43321</b> | DWG. NO.<br><b>CA-085FNMMN</b> |
| PROJECTION<br>  | COLOR VARIATIONS<br>MAY OCCUR   | SCALE: NONE                           | CAD FILE: CA-085FNMMN.SLDDRW                              | SHEET 1 OF 1                                     |                          |                                |