


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/19/2023	DFRISIELLO	GUTTADAURO



ITEM NUMBER	LENGTH, FT [mm]	TOLERANCE
AMC14C13RA-15-3F	3.0 [915.0]	± .79 [20.0]
AMC14C13RA-15-6F	6.0 [1830.0]	± .79 [20.0]
AMC14C13RA-15-10F	10.0 [3050.0]	± .79 [20.0]

NOTES:

UL FILE: E234956  
RATING: 15A/250V

- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY: DFRISIELLO CHECKED BY: ELAMOTT APPROVED BY: GUTTADAURO	DATE 04/19/2023 04/19/2023 04/19/2023	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY <b>POWER CORD</b>		PRODUCT DESCRIPTION <b>C14 to RA C13, Antimicrobe Jkt, 15 A</b>
THIRD-ANGLE PROJECTION 	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>AMC14C13RA-15</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: AMC14C13RA-15.SLDDRW		SHEET 1 OF 1