


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

8 7 6 5 4 3 2 1

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR

D

D



C

C

B

B

PART NUMBER	LENGTH METER [FEET]
FCA-M1SP-LCSC-01M	1.0 [3.28]
FCA-M1SP-LCSC-02M	2.0 [6.56]
FCA-M1SP-LCSC-03M	3.0 [9.84]
FCA-M1SP-LCSC-05M	5.0 [16.40]
FCA-M1SP-LCSC-10M	10.0 [32.81]

B

B

A

A

NOTES:

1. LC CONNECTOR ASSEMBLY POLISH TYPE: UPC  
SC CONNECTOR ASSEMBLY POLISH TYPE: UPC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-com an INFINITe brand	CATEGORY	PRODUCT DESCRIPTION
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY MVEERAPPAN	09/28/2021			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS .XX = ± .02 [5]      ± 1/32 .XXX = ± .005 [13]      ANGLES ± 1°	CHECKED BY DFRISIELLO	09/28/2021			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	APPROVED BY PHOSPODAR	09/28/2021			
THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. FCA-M1SP-LCSC	REV. <b>A</b>
	SCALE: NONE	CAD FILE: FCA-M1SP-LCSC.SLDDRW			SHEET 1 OF 1