


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISI

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-S2SR-FCASTU-01M	1.0 [3.28]
FCA-S2SR-FCASTU-02M	2.0 [6.56]
FCA-S2SR-FCASTU-03M	3.0 [9.84]
FCA-S2SR-FCASTU-05M	5.0 [16.40]
FCA-S2SR-FCASTU-10M	10.0 [32.81]
FCA-S2SR-FCASTU-15M	15.0 [49.21]


NOTES:

1. FC CONNECTOR 1 ASSEMBLY POLISH TYPE: APC.
2. ALL CONNECTORS ACCCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = $+1$ [25] / -0
 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
 > 300 [7620] = $+5%$ / -0

ALL OTHER DIMENSIONAL TOLERANCES:
 $.X = \pm .2$ [5] FRACTIONS
 $.XX = \pm .02$ [5] $\pm 1/32$
 $.XXX = \pm .005$ [1.3] ANGLES $\pm 1^\circ$



THIRD-ANGLE PROJECTION

COLOR VARIATIONS
MAY OCCUR

APPROVALS

DATE

DRAWN BY
MVEERAPPAN

CHECKED BY
DFRISIELLO

APPROVED BY
PHOSPODAR

CATEGORY

PRODUCT DESCRIPTION

FIBER OPTICS

ITEM NO.

SIZE

43321

CAGE CODE

FCA-S2SR-FCASTU

ITEM NO.

REV.

A

SCALE: NONE

CAD FILE: FCA-S2SR-FCASTU.SLDDRW

SHEET 1 OF 1



50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936