


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6899: UPD FORMAT/PKG. CONTACTS FROM 30u" GOLD TO GOLD FLASH	6/14/13	D. DESJARDIN
F	ECN 7529: CHG'D PANTONE TO 424C FROM 422C	7/23/14	D. CASTRO




"P1"
2X IEEE-1394
TYPE 1 (6 PIN)
MALE CONNECTOR

2X, MOLDED HOOD
AND STRAIN RELIEF
PVC, GRAY (PANTONE 424C)

U.L. STYLE 20276,
TWO, 28 AWG INDIVIDUALLY SHIELED TWISTED PAIR
TWO, 22 AWG STRANDED COPPER CONDUCTORS WITH OVERALL
ALUM/POLY SHIELD PLUS TINNED COPPER BRAID SHIELD
JACKET: PVC, GRAY (PANTONE 424C)

2X L-COM LOGO
BOTH SIDES

"P2"



MODEL NUMBER	LENGTH	
	METERS	FEET
CSM94-05M	0.5	1.64
CSM94-1M	1.0	3.28
CSM94-2M	2.0	6.56
CSM94-3M	3.0	9.84
CSM94-5M	5.0	16.40

NOTES:

1. CABLE ASSEMBLY CONSTRUCTED TO MEET THE REQUIREMENTS OF THE IEEE-1394 (FIREWIRE) SPECIFICATION.
2. CONTACT FINISH: GOLD FLASH.
3. TWISTED PAIRS INDIVIDUALLY SHIELDED. SHIELDS TIED TOGETHER AND TIED TO PIN 2.
4. CABLE OVERALL SHIELD CONNECTED TO METAL SHELLS OF BOTH PLUGS. OVERALL SHIELD ISOLATED FROM TWISTED PAIRS' SHIELDS.
5. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
6. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS DRAWN BY D PARHAM CHECKED BY T CLARK APPROVED BY Z W	DATE 8/15/2001 8/16/2001 9/14/2001	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CATEGORY I/O PRODUCTS			PRODUCT DESCRIPTION CBL, IEEE1394 TYPE 1/1		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A		FSCM NO. 43321	DWG. NO. CSM94
	PROJECTION 	SCALE: NONE		CAD FILE: CSM94.SLDDRW	SHEET 1 OF 1	