







THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION |     |                 |            |            |           |
|----------|-----|-----------------|------------|------------|-----------|
| ZONE     | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED  |
|          | A   | INITIAL RELEASE | 03/06/2023 | HBAKKE     | PHOSPODAR |




RECOMMENDED  
PANEL CUTOUT

#### NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DUST CAPS NOT SHOWN.
3. RECOMMENDED PANEL THICKNESS: .05-.07" [1.2-1.7mm]
4. STANDARDS: IEC 61754-7-MPO, TIA/EIA 604-5 TYPE MPO, TELCORDIA GR-1435-CORE
5. INSERTION LOSS: <0.5dB
6. OPERATING/STORAGE TEMPERATURE: -40 TO +85°C
7. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
8. WHITE MARK FOR KEY UP-KEY DOWN.

#### REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

|                                                                                                                                                                                                                                                                                                                                                                                                                          |                                                                |            |                                                                                                                          |                    |                                                                                                      |              |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------|------------|--------------------------------------------------------------------------------------------------------------------------|--------------------|------------------------------------------------------------------------------------------------------|--------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]<br><br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0<br><br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ±.2 [5]   FRACTIONS ± 1/32<br>.XX = ±.02 [.5]   ANGLES ± 1°<br>.XXX = ±.005 [.13] | APPROVALS                                                      | DATE       | <div><div>L-com™</div><div>an INFINITI® brand</div></div>                                                                |                    | 50 High Street, West Mill,<br>North Andover, MA 01845 USA<br>Phone: 1.800.341.5266<br>1.978.682.6936 |              |
|                                                                                                                                                                                                                                                                                                                                                                                                                          | DRAWN BY<br>HBAKKE                                             | 03/06/2023 |                                                                                                                          |                    |                                                                                                      |              |
|                                                                                                                                                                                                                                                                                                                                                                                                                          | CHECKED BY<br>DMAY                                             | 03/06/2023 | CATEGORY                                                                                                                 |                    |                                                                                                      |              |
|                                                                                                                                                                                                                                                                                                                                                                                                                          | APPROVED BY<br>REVANGELIS                                      | 03/06/2023 |                                                                                                                          |                    |                                                                                                      |              |
| THIRD-ANGLE PROJECTION<br>                                                                                                                                                                                                                                                                                                          | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY |            | PRODUCT DESCRIPTION<br>MPO 6 Port Cluster Adapter, 12F/24F, High Density<br>Reduced Height, Key up-Key Down, Black, Aqua |                    |                                                                                                      |              |
|                                                                                                                                                                                                                                                                                                                                                                                                                          | COLOR VARIATIONS<br>MAY OCCUR                                  |            | SIZE<br>A                                                                                                                | CAGE CODE<br>43321 | ITEM NO.<br>FOA-860-AQU                                                                              | REV<br>A     |
|                                                                                                                                                                                                                                                                                                                                                                                                                          |                                                                |            | SCALE: NONE                                                                                                              |                    | CAD FILE: FOA-860-AQU.SLDDRW                                                                         | SHEET 1 OF 1 |