


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISI

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2021	PHOSPODAR



PART NUMBER	LENGTH METER [FEET]
FCA-S1SR-LCLC-01M	1.0 [3.28]
FCA-S1SR-LCLC-02M	2.0 [6.56]
FCA-S1SR-LCLC-03M	3.0 [9.84]
FCA-S1SR-LCLC-05M	5.0 [16.40]
FCA-S1SR-LCLC-10M	10.0 [32.81]
FCA-S1SR-LCLC-15M	15.0 [49.21]

NOTES:

1. LC CONNECTOR ASSEMBLY POLISH TYPE: UPC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY MVEERAPPAN	09/28/2021
	CHECKED BY DFRISIELLO	09/28/2021
	APPROVED BY PHOSPODAR	09/28/2021
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°		
THIRD-ANGLE PROJECTION 		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
COLOR VARIATIONS MAY OCCUR		

L-COM
an INFINITE brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

FIBER OPTICS

CA LC-LC 9/125 SINGLEMODE

ITEM NO. FCA-S1SR-LCLC

REV. A

SIZE A CAGE CODE 43321 SCALE: NONE CAD FILE: FCA-S1SR-LCLC.SLDDRW SHEET 1 OF 1