


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
D	REVISED NOTES ECN 1149	06/28/02	MCCORMICK
E	REVISED CABLE MARKERS ECN 1274	01/02/03	MCCORMICK
F	REVISED CABLE TO 1.6mm CONSTRUCTION FROM 3.0mm	09/01/05	MCCORMICK
G	REVISED CABLE TO 1.6mm CONSTRUCTION FROM 3.0mm	11/28/06	MCCORMICK




PART #	LENGTH FEET [METERS]
FODST-MT-01	3.28 [1.0]
FODST-MT-02	6.56 [2.0]
FODST-MT-03	9.84 [3.0]
FODST-MT-04	13.12 [4.0]
FODST-MT-05	16.40 [5.0]

**OUTLINE DRAWING**

NOTES:  
 1. CONNECTOR ASSEMBLY USES A PC POLISH.  
 2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP (NOT SHOWN).

DIMENSIONS ARE IN INCHES [mm]  
 UNLESS OTHERWISE SPECIFIED,  
 TOLERANCES TO BE:  
 .X ±1 [2.5] ANGLES ±2°  
 .XX ±.05 [1.3]  
 .XXX ±.005 [0.13]  
 OVERALL CABLE LENGTH TOL:  
 ≤60 [1524] +3 [76.2] / - 0  
 >60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY C.MCCORMICK	01/05/2001
CHECKED BY DFP	01/05/2001
APPROVED BY R.CARRICK	01/05/2001

CONFIGURATION DETAILS OF  
 UNDIMENSIONED FEATURES  
 MAY VARY

**L-com**  
 CONNECTIVITY PRODUCTS

45 BEECHWOOD DRIVE  
 NORTH ANDOVER, MA  
 01845

CATEGORY: FIBER OPTIC

PRODUCT DESCRIPTION: 62.5/125 MTRJ CABLE ASSY

SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>FODST-MT-01-OD1</b>	REV. <b>G</b>
------------------	--------------------------	------------------------------------	------------------

SCALE: NONE | CAD FILE: FODST-MT-01-OD1.SLDDRW | SHEET 1 OF 1