



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/20/11	D.GRIFFIN
B	ECN 7158: UPDATED OVERMOLD DESIGN AND REVISED ROHS NOTE	11/14/13	D. DESJARDIN



2X HDMI MALE  
19 PIN CONNECTOR  
GOLD PLATED CONTACTS



PART NUMBER	LENGTH	
	METERS	FEET
HDCAMMZ-0.5	0.5	1.64
HDCAMMZ-1	1.0	3.28
HDCAMMZ-2	2.0	6.56
HDCAMMZ-3	3.0	9.84
HDCAMMZ-4	4.0	13.12
HDCAMMZ-5	5.0	16.40

**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	10/18/2011		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY D. CASTRO	10/18/2011	PRODUCT DESCRIPTION	
	APPROVED BY P. McNEIL	10/18/2011	CA HDMI M-M LSZH	
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE <b>A</b>	FSCM NO. <b>43321</b>
	COLOR VARIATIONS MAY OCCUR		DWG. NO. HDCAMMZ	REV. <b>B</b>
SCALE: NONE			CAD FILE: HDCAMMZ.SLDDRW	
			SHEET 1 OF 1	