


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/02/2002	C.MCCORMICK
B	ECN# 2248 CONSTRUCTION FROM 1.6mm TO 3.0mm	11/14/05	MCCORMICK
.	.	.	.
.	.	.	.



PART NUMBER	LENGTH METERS
FODPLC-01	1.0
FODPLC-02	2.0
FODPLC-03	3.0
FODPLC-04	4.0
FODPLC-05	5.0

NOTES:

- 1.0 **TEST:**
 - 1.1 INSERTION LOSS TESTED AT 1300nm WITH A <-1.0 dB RESULT.
- 2.0 **PACKAGING:**
 - 2.1 THE PRODUCT SHALL BE PRESERVED & PACKAGED IN A MANNER WHICH WILL AFFORD ADEQUATE PROTECTION AGAINST CORROSION, DETERIORATION, AND PHYSICAL DAMAGE DURING SHIPMENT.
 - 2.2 INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG DEPICTED ON [1AN01-001-OD1](#) . MARK EACH BAG PER [LSP-010-1](#)
- 3.0 **WORKMANSHIP:**
 - 3.1 CABLE ASSEMBLIES SHALL BE MANUFACTURED IN SUCH A MANNER AS TO BE UNIFORM IN QUALITY AND SHALL BE FREE FROM DEFECTS THAT WILL ADVERSELY AFFECT LIFE, SERVICEABILITY, OR APPEARANCE.
- 4.0 **VISUAL AND MECHANICAL:**
 - 4.1. CABLE ASSEMBLIES SHALL BE INSPECTED TO VERIFY COMPLIANCE TO THIS DRAWING.
- 5.0 **MANUFACTURING:**
 - 5.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES TOLERANCES ARE:
 X ±.1
 XX ±.05
 XXX ±.005
 CABLE LENGTH TOLERANCE
 ≤300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	12/02/2002
CHECKED BY D.PARHAM	12/02/2002
APPROVED BY R.CARRICK	12/02/2002

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION LC PLENUM CABLE ASSEMBLY			
DRAWING TITLE OUTLINE DRAWING			
SIZE A	FSCM NO. 43321	DWG. NO. FODPLC-1-OD1	REV. B
SCALE: NONE		CAD FILE: FODPLC-1-OD1.SLDDRW	
			SHEET 1 OF 1

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY