


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/23/12	D.GRIFFIN



DIE SET NUMBER	COLOR CODE	DESCRIPTION
2990004-01	RED	4 POSITION MODULAR PLUG
2990005-01	BLUE	6 POSITION MODULAR PLUG
2990006-01	YELLOW	8 POSITION MODULAR PLUG
2990008-01	WHITE	10S POSITION MODULAR PLUG

RATCHET RELEASE LEVER

7.5  
[190.5]

NOTES:

- TOOL HAS CUTTING AND STRIPPING FEATURE.
- ROUND AND FLAT CABLE COMPATIBILITY.
- ALLEN WRENCH INCLUDED.

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO	DATE 2/21/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY J.RUST	DATE 2/21/12	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION CRIMP TOOL W/DIE RJ45 C6 NS	APPROVED BY D.GALLAGHER
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>HTS7508C6</b>
SCALE: NONE		CAD FILE: HTS7508C6.SLDDRW	
			SHEET 1 OF 1