


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION					
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	05/08/2023	BPUCHASKI	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS , ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

<div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</div> <div>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</div> <div>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°</div> <div>THIRD-ANGLE PROJECTION </div>	<div>APPROVALS</div> <div>DRAWN BY BPUCHASKI</div> <div>CHECKED BY KLEITLEIN</div> <div>APPROVED BY AGANWANI</div>	<div>DATE</div> <div>05/08/2023</div> <div>05/08/2023</div> <div>05/08/2023</div>	<div> an INFINITI® brand</div> <div>CATEGORY</div> <div>COAXIAL</div>	<div>50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936</div>	
	<div>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</div>		<div>PRODUCT DESCRIPTION</div> <div>SMB Plug to SMB Jack Bulkhead Cable Using RG316 Coax</div>		
	<div>COLOR VARIATIONS MAY OCCUR</div>	<div>SIZE A</div>	<div>CAGE CODE 43321</div>	<div>ITEM NO. LCCA31293</div>	<div>REV A</div>
		<div>SCALE: NONE CAD FILE: LCCA31293.SLDDRW</div>			<div>SHEET 1 OF 1</div>