




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS |                        |            |           |
|-----------|------------------------|------------|-----------|
| REV       | DESCRIPTION            | DATE       | APPROVED  |
| A         | REV A DRAWING RELEASED | 04/19/2019 | MMARTINEZ |
|           |                        |            |           |
|           |                        |            |           |



NOTES:

1. DIMENSIONS FOR REFERENCE ONLY.
2. MATERIAL: .06 THICK COLD ROLLED STEEL.
3. PANEL FINISH: FLAT BLACK POWDER COAT.
4. SILKSCREEN COLOR: WHITE.
5. PANEL ASSEMBLY SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.

|  |  |  |  |                   |
|--|--|--|--|-------------------|
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONS ARE IN INCHES [mm]<br><br>OVERALL CABLE LENGTH TOLERANCE:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0%<br><br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5.08]<br>.XX = ± .02 [51]<br>.XXX = ±.005 [13] | APPROVALS  | DATE   |  50 HIGH STREET<br>NORTH ANDOVER, MA<br>01845 |                   |
|  | DRAWN BY<br>DZINN  | 04/02/2019   |  |                   |
|  | CHECKED BY<br>DFRISIELLO                                       | 04/02/2019   | CATEGORY<br><br>RACK PANELS  |                   |
|  | APPROVED BY<br>MMARTINEZ                                       | 04/02/2019   |  |                   |
|   | CONFIGURATION DETAILS OF<br>UNDIMENSIONED FEATURES<br>MAY VARY |  | PRODUCT DESCRIPTION<br><br>PNL,1U RACK w/12 C6A CPLR   |                   |
|  |  |  | SIZE<br>A  | FSCM NO.<br>43321 |
|  | COLOR VARIATIONS<br>MAY OCCUR                                  | DWG. NO.<br>PR175-C6A-12                                   | REV.<br>A  |                   |
|  |  | SCALE: NONE   CAD FILE: PR175-C6A-12.SLDDRW   SHEET 1 OF 1 |  |                   |