


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/24/2021	PHOSPODAR



WIRING MAP

J1	J2	J3	COLOR	J3	J4
		12	BLUE		1
		11	ORANGE		2
		10	GREEN		3
		9	BROWN		4
12			GRAY		5
11			WHITE		6
2			RED		7
1			BLACK		8
	4		YELLOW		9
	3		PURPLE		10
	2		ROSE		11
	1		AQUA		12
12			BLUE w/TRACER	1	
11			ORANGE w/TRACER	2	
10			GREEN w/TRACER	3	
9			BROWN w/TRACER	4	
10			GRAY w/TRACER	5	
9			WHITE w/TRACER	6	
4			RED w/TRACER	7	
3			BLACK w/TRACER	8	
4			YELLOW w/TRACER	9	
3			PURPLE w/TRACER	10	
2			ROSE w/TRACER	11	
1			AQUA w/TRACER	12	



PART NUMBER	LENGTH METERS (FEET)	BREAKOUT METERS (FEET)
MPM308212SMZ-CA-1	1.0 (3.28)	0.3 (1.00)
MPM308212SMZ-CA-3	3.0 (9.84)	0.6 (2.00)
MPM308212SMZ-CA-5	5.0 (16.40)	
MPM308212SMZ-CA-10	10.0 (32.81)	

- NOTES:
- MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC.
 - ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
 - PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY: DZINN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR	DATE 03/24/2021 03/24/2021 03/24/2021	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION FIBER AG CONV HARNESS, 3XMP08 (M) TO 2XMP012 (M)
SIZE A		CAGE CODE 43321	ITEM NO. MPM308212SMZ-CA	REV. A
SCALE: NONE		CAD FILE: MPM308212SMZ-CA.SLDDRW		SHEET 1 OF 1