





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	01/17/2024	BZHANG	GUTTADAURO



- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

LSZH CABLE CHARACTERISTICS:
 FLAME RATING: IEC 60332-1
 CORROSIVE GAS: IEC 60754
 SMOKE EMISSION: IEC 61034

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY BZHANG 10/05/2023 CHECKED BY GUTTADAURO 10/05/2023 APPROVED BY GUTTADAURO 10/05/2023	CATEGORY TELECOM/MODULAR		PRODUCT DESCRIPTION C6A LSZH F/UTP STR-DWN	
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. TRD695ASZRA1	REV. A
SCALE: NONE		CAD FILE: TRD695ASZRA1.SLDDRW		SHEET 1 OF 2	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD695ASZRA1BLK-1	BLACK	1.0 [0.30]	TRD695ASZRA1RED-1	RED	1.0 [0.30]	TRD695ASZRA1GRY-1	GRAY	1.0 [0.30]
TRD695ASZRA1BLK-2	BLACK	2.0 [0.61]	TRD695ASZRA1RED-2	RED	2.0 [0.61]	TRD695ASZRA1GRY-2	GRAY	2.0 [0.61]
TRD695ASZRA1BLK-3	BLACK	3.0 [0.91]	TRD695ASZRA1RED-3	RED	3.0 [0.91]	TRD695ASZRA1GRY-3	GRAY	3.0 [0.91]
TRD695ASZRA1BLK-5	BLACK	5.0 [1.52]	TRD695ASZRA1RED-5	RED	5.0 [1.52]	TRD695ASZRA1GRY-5	GRAY	5.0 [1.52]
TRD695ASZRA1BLK-7	BLACK	7.0 [2.13]	TRD695ASZRA1RED-7	RED	7.0 [2.13]	TRD695ASZRA1GRY-7	GRAY	7.0 [2.13]
TRD695ASZRA1BLK-10	BLACK	10.0 [3.05]	TRD695ASZRA1RED-10	RED	10.0 [3.05]	TRD695ASZRA1GRY-10	GRAY	10.0 [3.05]
TRD695ASZRA1BLK-15	BLACK	15.0 [4.57]	TRD695ASZRA1RED-15	RED	15.0 [4.57]	TRD695ASZRA1GRY-15	GRAY	15.0 [4.57]
TRD695ASZRA1BLK-20	BLACK	20.0 [6.10]	TRD695ASZRA1RED-20	RED	20.0 [6.10]	TRD695ASZRA1GRY-20	GRAY	20.0 [6.10]



50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

TELECOM/MODULAR

PRODUCT DESCRIPTION

C6A LSZH F/UTP STR-DWN

SIZE	CAGE CODE	ITEM NO.	REV.
A	43321	TRD695AZRA1	A
SCALE: NONE		CAD FILE: TRD695ASZRA1.SLDDRW	SHEET 2 OF 2