



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04-01-2021	GUTTADAURO



2X NYLON ANTIBACTERIAL RJ45 50UM GOLD PLATED CONTACTS



Cat 6a. FOUR TWISTED PAIR, STRANDED BARE COPPER CONDUCTOR TYPE - 24AWG(7/0.20±0.008MM), STRANDED BC INSULATION - HDPE
 CABLE JACKET: ANTIBACTERIAL PVC
 TEMPERATURE RATING -20°C TO +75°C.
 VOLTAGE RATING - 30V.
 WIRING SCHEME -TIA568B.

PART NUMBER	LENGTH FEET [METERS]
TRM695A-WHT-05F	0.5 [0.15]
TRM695A-WHT-1F	1.0 [0.30]
TRM695A-WHT-2F	2.0 [0.60]
TRM695A-WHT-3F	3.0 [0.91]
TRM695A-WHT-5F	5.0 [1.52]
TRM695A-WHT-7F	7.0 [2.13]
TRM695A-WHT-10F	10.0 [3.04]
TRM695A-WHT-15F	15.0 [4.57]
TRM695A-WHT-20F	20.0 [6.09]
TRM695A-WHT-25F	25.0 [7.62]
TRM695A-WHT-50F	50.0 [15.24]
TRM695A-WHT-60F	60.0 [18.28]
TRM695A-WHT-70F	70.0 [21.33]
TRM695A-WHT-80F	80.0 [24.38]
TRM695A-WHT-100F	100.0 [30.48]

NOTES:

ANTIBACTERIAL TEST METHOD:

ISO 22196:2011 MEASUREMENT OF ANTIBACTERIAL ACTIVITY ON PLASTICS AND OTHER NON-POROUS SURFACES.

TEST ORGANISM:

ESCHERICHIA COLI ATCC 8738
 STAPHYLOCOCCUS AUREUS ATCC 6538P

ANTIBACTERIAL ACTIVITY RATE:

ESCHERICHIA COLI > 99.9%
 STAPHYLOCOCCUS AUREUS > 99.9%

MISCELLANEOUS:

CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY MVEERAPPAN CHECKED BY SPAN APPROVED BY GUTTADAURO	DATE 04-01-2021 04-01-2021 04-01-2021	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
	COLOR VARIATIONS MAY OCCUR			PRODUCT DESCRIPTION Cat6A Antibacterial UTP RJ45 24STR CM PVC WHT
	THIRD-ANGLE PROJECTION 	SIZE A CAGE CODE 43321 SCALE: NONE		DWG. NO. TRM695A-WHT CAD FILE: TRM695A-WHT.SLDDRW