

6

5

4

3



2

1


| REVISION |     |                       |           |            |          |
|----------|-----|-----------------------|-----------|------------|----------|
| ZONE     | REV | DESCRIPTION           | DATE      | CHANGED BY | APPROVED |
|          | B   | UPDATED PER ECO-14743 | 7/16/2025 | HBAKKE     | DREBECK  |

F  
E  
D  
C  
B  
A

F  
E  
D  
C  
B  
A




LOGO/ITEM # LABEL  
WITH ILS-100-05,  
SEE NOTE 1



LED VISUAL  
STATUS INDICATORS

SURGE COUNTER DISPLAY

AC SERVICE & REMOTE STATUS WIRES  
30" LENGTH EA CONDUCTOR



NOTES:  
1. SEE LABEL SPECIFICATION ILS-100.  
FOR INTERNAL REFERENCE ONLY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:  
X = ±.2 [5] | FRACTIONS ± 1/32  
XX = ±.02 [0.5] | ANGLES ± 1°  
.XXX = ±.005 [0.13]

CABLE LENGTH TOLERANCES:  
≤12 [305] = +1 [25] / -0  
>12 [305] ≤ 60 [1524] = +2 [51] / -0  
>60 [1524] ≤ 120 [3048] = +4 [102] / -0  
>120 [3048] ≤ 300 [7620] = +6 [152] / -0  
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE  
UN-DIMENSIONED/NON-CRITICAL FEATURES  
MAY VARY IN SIZE AND LOCATION  
COLORS MAY VARY



an INFINITE® brand  
Website: www.L-com.com  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

|       |        |
|-------|--------|
| SCALE | SHEET  |
| NONE  | 1 OF 1 |

DESCRIPTION  
AC SPD TYPE 2 EMI FILTERED 480/277Vac WYE 200kA/PHASE

|      |           |          |                    |     |
|------|-----------|----------|--------------------|-----|
| SIZE | CAGE CODE | DRAWN BY | ITEM NO.           | REV |
| A    | 43321     | HBAKKE   | SP200-T2F-2773Y-LC | B   |

6

5

4

3

2

1