



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISION |     |                 |            |            |            |
|----------|-----|-----------------|------------|------------|------------|
| ZONE     | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED   |
|          | A   | INITIAL RELEASE | 01/17/2024 | BZHANG     | GUTTADAURO |



**NOTES:**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.


**LSZH CABLE CHARACTERISTICS:**

FLAME RATING: IEC 60332-1  
 CORROSIVE GAS: IEC 60754  
 SMOKE EMISSION: IEC 61034

|   |   |  |   |
|---|---|--|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]<br>OVERALL CABLE LENGTH TOLERANCES:<br>≤12 [305] = +1 [25] / -0<br>>12 [305] ≤60 [1524] = +2 [51] / -0<br>>60 [1524] ≤120 [3048] = +4 [102] / -0<br>>120 [3048] ≤300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0<br>ALL OTHER DIMENSIONAL TOLERANCES:<br>.X = ± .2 [5]   FRACTIONS ± 1/32<br>.XX = ± .02 [.5]   ANGLES ± 1°<br>.XXX = ± .005 [.13] | APPROVALS<br>DRAWN BY BZHANG<br>CHECKED BY GUTTADAURO<br>APPROVED BY GUTTADAURO | DATE<br>10/05/2023<br>10/05/2023<br>10/05/2023         | 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936                          |
|   | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY                        |  |   |
| THIRD-ANGLE PROJECTION<br>  | COLOR VARIATIONS MAY OCCUR  | SIZE <b>A</b><br>CAGE CODE <b>43321</b><br>SCALE: NONE | PRODUCT DESCRIPTION<br><b>C6A LSZH F/UTP STR-LFT</b><br>ITEM NO. <b>TRD695ASZRA6</b><br>CAD FILE: TRD695ASZRA6.SLDDRW |
|   |   | SHEET 1 OF 2   | REV. <b>A</b>   |

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| PART NUMBER        | COLOR | LENGTH FEET [METERS] | PART NUMBER        | COLOR | LENGTH FEET [METERS] | PART NUMBER        | COLOR | LENGTH FEET [METERS] |
|--------------------|-------|----------------------|--------------------|-------|----------------------|--------------------|-------|----------------------|
| TRD695ASZRA6BLK-1  | BLACK | 1.0 [0.30]           | TRD695ASZRA6RED-1  | RED   | 1.0 [0.30]           | TRD695ASZRA6GRY-1  | GRAY  | 1.0 [0.30]           |
| TRD695ASZRA6BLK-2  | BLACK | 2.0 [0.61]           | TRD695ASZRA6RED-2  | RED   | 2.0 [0.61]           | TRD695ASZRA6GRY-2  | GRAY  | 2.0 [0.61]           |
| TRD695ASZRA6BLK-3  | BLACK | 3.0 [0.91]           | TRD695ASZRA6RED-3  | RED   | 3.0 [0.91]           | TRD695ASZRA6GRY-3  | GRAY  | 3.0 [0.91]           |
| TRD695ASZRA6BLK-5  | BLACK | 5.0 [1.52]           | TRD695ASZRA6RED-5  | RED   | 5.0 [1.52]           | TRD695ASZRA6GRY-5  | GRAY  | 5.0 [1.52]           |
| TRD695ASZRA6BLK-7  | BLACK | 7.0 [2.13]           | TRD695ASZRA6RED-7  | RED   | 7.0 [2.13]           | TRD695ASZRA6GRY-7  | GRAY  | 7.0 [2.13]           |
| TRD695ASZRA6BLK-10 | BLACK | 10.0 [3.05]          | TRD695ASZRA6RED-10 | RED   | 10.0 [3.05]          | TRD695ASZRA6GRY-10 | GRAY  | 10.0 [3.05]          |
| TRD695ASZRA6BLK-15 | BLACK | 15.0 [4.57]          | TRD695ASZRA6RED-15 | RED   | 15.0 [4.57]          | TRD695ASZRA6GRY-15 | GRAY  | 15.0 [4.57]          |
| TRD695ASZRA6BLK-20 | BLACK | 20.0 [6.10]          | TRD695ASZRA6RED-20 | RED   | 20.0 [6.10]          | TRD695ASZRA6GRY-20 | GRAY  | 20.0 [6.10]          |

|   |                           |   |                  |
|---|---------------------------|---|------------------|
|    |                           | 50 High Street, West Mill,<br>North Andover, MA 01845 USA.<br>Phone: 1.800.341.5266<br>1.978.682.6936 |                  |
| CATEGORY<br><p style="text-align: center;"><b>TELECOM/MODULAR</b></p>                   |                           |   |                  |
| PRODUCT DESCRIPTION<br><p style="text-align: center;"><b>C6A LSZH F/UTP STR-LFT</b></p> |                           |   |                  |
| SIZE<br><b>A</b>  | CAGE CODE<br><b>43321</b> | ITEM NO.<br><b>TRD695ASZRA6</b>   | REV.<br><b>A</b> |
| SCALE: NONE   |                           | CAD FILE: TRD695ASZRA6.SLDDRW   |                  |
|   |                           |   | SHEET 2 OF 2     |