

75 Ohm BNC Plug 1553 Connector Crimp/Solder Attachment
for Telco DS3 734A, BELDEN 1505A, VPM2000



LCCN10-03001-204

Configuration

- BNC Plug Connector
- MIL-STD-1553
- 75 Ohms
- Straight Body Geometry
- Telco DS3 734A, Belden 1505A, VPM2000 Interface Type
- Crimp/Solder Attachment
- 1553 Design

Features

- Twinax Connectivity
- Bayonet Coupling

Applications

- Robust Design
- Ease of Use
- Use in High Shock and Vibration Environment

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Insertion Loss		0.1		dB

Mechanical Specifications

Size

Length	1.00 in [25.40 mm]
Width	0.57 in [14.48 mm]
Height	0.57 in [14.48 mm]
Weight	0.03 lbs [11.79 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold 30 micro inches ASTM-B-488
Insulation	Teflon	
Outer Conductor	Phosphor Bronze	ASTM-B-488
Body	Brass	Nickel ASTM-B-733
Gasket	Rubber	
Crimp Sleeve	Brass	Nickel

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[75 Ohm BNC Plug 1553 Connector Crimp/Solder Attachment for Telco DS3 734A, BELDEN 1505A, VPM2000 LCCN10-03001-204](#)

75 Ohm BNC Plug 1553 Connector Crimp/Solder Attachment
for Telco DS3 734A, BELDEN 1505A, VPM2000



LCCN10-03001-204

Environmental Specifications

Temperature

Operating Range

-55deg C to +200deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

75 Ohm BNC Plug 1553 Connector Crimp/Solder Attachment for Telco DS3 734A, BELDEN 1505A, VPM2000 from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 75 Ohm BNC Plug 1553 Connector Crimp/Solder Attachment for Telco DS3 734A, BELDEN 1505A, VPM2000 LCCN10-03001-204

URL: <https://www.l-com.com/75-ohm-bnc-plug-1553-connector-crimp-solder-attachment-telco-ds3-734a-belden-1505a-vpm2000-lccn10-03001-204-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

