

## Reverse Polarity SMA Female Connector Crimp/ Solder Attachment for RG188-DS, RG316-DS



### LCCN45919

#### Configuration

- SMA Female Reverse Polarity Connector
- 50 Ohms
- Straight Body Geometry
- RG188-DS, RG316-DS Interface Type
- Crimp/Solder Attachment

#### Features

- Gold Plated Contact
- Reverse Polarity

#### Applications

- General Purpose Test
- Custom Cable Assemblies

#### Description

L-com's LCCN45919 , SMA, Standard, Connector is part of our full line of RF components available for same-day shipping. The female reverse polarity configuration uses a female connector body with a male inner contact pin. Our reverse polarity SMA female connector LCCN45919 datasheet specifications and drawing with dimensions are shown below in this PDF. L-com's broad catalog of RF, micro-wave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, L-com has the right connector for the job. L-com can also expertly build your custom cable assemblies for you and ship same-day.

#### Mechanical Specifications

##### Size

Length	0.91 in [23.11 mm]
Width	0.31 in [7.92 mm]
Weight	0.01 lbs [2.72 g]

#### Material Specifications

Description	Material	Plating
Insulation	PTFE	
Body	Brass	Nickel

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[Reverse Polarity SMA Female Connector Crimp/Solder Attachment for RG188-DS, RG316-DS LCCN45919](#)

Reverse Polarity SMA Female Connector Crimp/  
Solder Attachment for RG188-DS, RG316-DS



**LCCN45919**

---

**Environmental Specifications**

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Reverse Polarity SMA Female Connector Crimp/Solder Attachment for RG188-DS, RG316-DS from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Reverse Polarity SMA Female Connector Crimp/Solder Attachment for RG188-DS, RG316-DS LCCN45919

URL: <https://www.l-com.com/reverse-polarity-sma-female-connector-crimp-solder-attachment-rg188-ds-rg316-ds-lccn45919-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

