

BNC Male Right Angle Connector Crimp/Solder Attachment for RG188-DS, RG316-DS



LCCN45952

Configuration

- BNC Male Connector
- 50 Ohms
- Right Angle Body Geometry
- RG188-DS, RG316-DS Interface Type
- Crimp/Solder Attachment

Features

- Gold Plated Contact

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

L-com's LCCN45952 Right Angle, BNC, Standard, Connector is part of our full line of RF components available for same-day shipping. Its right angle body geometry allows for easier connections in tight spaces. Our BNC male right angle connector LCCN45952 datasheet specifications and drawing with dimensions are shown below in this PDF. L-com's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, L-com has the right connector for the job. L-com can also expertly build your custom cable assemblies for you and ship same-day.

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width	0.57 in [14.48 mm]
Height	1.06 in [26.92 mm]
Weight	0.06 lbs [27.67 g]

Material Specifications

Description	Material	Plating
Insulation	PTFE	
Body	Brass	Nickel

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[BNC Male Right Angle Connector Crimp/Solder Attachment for RG188-DS, RG316-DS LCCN45952](#)

BNC Male Right Angle Connector Crimp/Solder
Attachment for RG188-DS, RG316-DS

LCCN45952



Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

BNC Male Right Angle Connector Crimp/Solder Attachment for RG188-DS, RG316-DS from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male Right Angle Connector Crimp/Solder Attachment for RG188-DS, RG316-DS LCCN45952

URL: <https://www.l-com.com/bnc-male-right-angle-connector-crimp-solder-attachment-rg188-ds-rg316-ds-lccn45952-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

