


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/27/17	R.CLARK



PIN ASSIGNMENT

A FEMALE	A FEMALE
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
SHELL	SHELL

**MATERIAL**  
 MODULE: SNAP IN MODULE, MOLDED ABS.  
 HOOD: MOLDED 25P PVC (SAME COLOR AS MODULE).  
 ADAPTER: USB AF/AF REV3.0, BLUE INSULATION, NICKEL PLATED SHELL.

- NOTES:**
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
  - COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		50 HIGH STREET NORTH ANDOVER, MA 01845
	DRAWN BY R.CLARK	09/27/17		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [13]	CHECKED BY D.FRISIELLO	9/28/2017	PRODUCT DESCRIPTION	
	APPROVED BY B.GATES	9/28/2017	ADPT, USB MODULE A-A F	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. <b>U3C00032</b>	REV. <b>A</b>
			SCALE: NONE	CAD FILE: U3C00032.SLDDRW
				SHEET 1 OF 1