



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/22/2020	GUTTADAURO
B	ECN 11058: REVISED ON/OFF BUTTON, POWER NOTE 1 TO 52-56V	03/29/2021	GUTTADAURO


PRODUCT INFORMATION LABEL
 LABEL PER ILS-100-03 SEE NOTE 1




BOTTOM



FRONT



TOP



REAR

NOTES:

1. LABEL PER ILS-100-03. FOR INTERNAL REFERENCE ONLY. LABEL LOCATION FOR REFERENCE ONLY.

INTERFACE:

- 10/100/1000-TX TRIPLE SPEED PORT, RJ45 FEMALE
- 100/1000-FX SFP TRANSCEIVER SLOT (SOLD SEPARATELY)

POWER:

1. POWER REQUIREMENTS: 52-56V DC
2. POE STANDARD: IEEE 802.3AT, POE+ (BACKWARDS COMPATIBLE WITH IEEE 802.3AF)
3. POE TYPE: MID-SPAN
4. POWER PIN ASSIGNMENT: 4/5(+), 7/8 (-)
5. POE POWER BUDGET 30W

ENVIRONMENTAL:

1. TEMPERATURE: 0°C - 50°C
2. RELATIVE HUMIDITY: 5% - 95% (NON-CONDENSING)

INSTALLATION OPTIONS:


1. WALL MOUNT
2. DIN-RAIL (OPTIONAL)

DIP SWITCH (PLEASE REBOOT SWITCH AFTER ADJUSTING DIP SWITCH)



1. ON: LINK FAULT PASSTHROUGH (LFP) ON
2. OFF: LINK FAULT PASSTHROUGH (LFP) OFF (SEE USER'S MANUAL FOR FURTHER DETAILS)

PACKAGE CONTENTS:

- MEDIA CONVERTER
- AC-DC ADAPTER



VENTING BOTH SIDES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY DZINN	09/22/2020		CATEGORY NETWORK EQUIPMENT	
CHECKED BY DFRISIELLO	09/22/2020	PRODUCT DESCRIPTION Gigabit Ethernet Media Converter with PoE+ 802.3at			
APPROVED BY GUITA DAURO	09/22/2020		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. MC-1GP+SFP	REV. B
SCALE: NONE		CAD FILE: MC-1GP+SFP.SLDDRW		SHEET 1 OF 1	