


D-Subminiature

Premium Lines:

CS2N, CS2NB, CS2H, CS2HB Series




For High EMI/RFI Applications

- Double shielded cable (foil + braid)
- 360° full metal shell around backshell
- Gold plated contacts
- Metal thumbscrews that can be hand tightened

Deluxe Lines:

CSMN, CSMNB, CHD Series




Industry Standard

- Shielded cable (foil)
- 360° copper foil shield around backshell
- Gold plated contacts
- Metal thumbscrews that can be hand tightened

Economy Line:

CSM Series



Our Most Economical Solution

- Shielded cable (foil)
- 360° foil shield around backshell
- Gold flash contacts
- Slotted machine screws

USB


Premium Line: CSMU Series



For High Power Applications

- 20 AWG power conductors for max current
- Double shielded cable (foil + braid)
- 30μ gold plated contacts

Deluxe Line: CAUBLK Series



For Medium Power Applications

- 24 AWG power conductors for medium current
- Double shielded cable (foil + braid)
- 30μ gold plated contacts

Economy Line: ECUSB Series




Industry Standard

- 26 AWG power conductors
- Double shielded cable (foil + braid)
- 30μ gold plated contacts
- Eight off-the-shelf lengths

Audio/Video

VGA



Premium/Deluxe Construction

Premium Line: CTLF3VGA Series



For High EMI/RFI Applications

- Double shielded cable + steel box in backshell + molded ferrite cores for superior EMI/RFI protection

Deluxe Lines: CTL3VGA, CTL3VGA-B (black) Series



For Medium EMI/RFI Applications

- Double shielded cable + steel box in backshell for increased EMI/RFI protection
- 45° versions available

Economy Line: CGSVGA Series



Industry Standard

- Double shielded cable
- 360° copper foil shield in backshell
- Off-the-shelf lengths from 3-50 feet

DVI

Premium Lines: CTLDVI, CTLDVI-DL Series

For High EMI/RFI & Professional Video Applications

- 30μ gold plated contacts
- Angled versions available
- Ferrites for EMI/RFI protection
- Available in DVI-D and DVI-I variations



Deluxe Lines: CGDVI, CGDVI-DL Series

Industry Standard

- Gold flash contacts
- Ferrites for EMI/RFI protection
- Fully molded backshells provide excellent strain relief




HDMI

Premium Line: HDCA Series

For Professional A/V Applications


- Six colors available
- 30μ gold plated contacts
- Angled versions available
- Support for Ethernet




Deluxe Line: CGHD Series

Industry Standard

- Gold flash contacts
- Support for Ethernet
- Seven off-the-shelf lengths from 0.3m to 5m



DIN and Mini DIN



Premium Construction

Premium Lines: DK226, DK238 Series



For High EMI/RFI Applications or Carrying Power

- Double shielded cable (foil + braid)
- 24AWG conductors
- Gold plated contacts
- Available only from L-com off-the-shelf

Economy Lines: CSMD6, CSMD8 Series



Industry Standard

- Shielded cable (foil)
- 28AWG conductors
- Gold plated contacts