








THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
G	ECN 4564: UPDATED DRAWING AND NEW FORMAT	03/02/2010	DFRISIELLO
H	ECN 5937: ADDED NOTE FOR PANEL MOUNTING	01/24/2012	DFRISIELLO
J	ECN 10934: REVISED GENDER CHANGE TO SOCKET SAVER IN LABEL NOTES	01/21/2021	MBLACKWOOD



RECOMMENDED PANEL OPENING
(MAX PANEL THICKNESS: 0.06")

NOTE: DIFFERENT STANDOFFS AND JACK SCREWS
ARE REQUIRED FOR PANEL MOUNTING.
SEE WWW.L-COM.COM OR MASTER CATALOG FOR DETAILS.



NOTES:

MATERIAL:
SHELL: STEEL
CONTACTS: COPPER ALLOY
HARDWARE: BRASS
INSULATOR: PBT FIBER REINFORCED (UL94V-0 RATED)

FINISH:
SHELL: TIN/NICKEL PLATED
CONTACTS: GOLD FLASH PLATED
HARDWARE: NICKEL PLATED

ELECTRICAL:
CURRENT RATING: 3 AMP

MISCELLANEOUS:
OPERATING TEMPERATURE RANGE: -55°C TO +105°C.
ALL CONTACTS ARE WIRED STRAIGHT THROUGH.
COMPONENT SHALL BE TESTED FOR CONTINUITY.

LABELING:
PANTONE 2945 BLUE. "L-COM" FONT MyriaMM REGULAR.
"SOCKET SAVER" FONT ARIAL BOLD, TEXT HEIGHTS; .085"
TEXT COLOR; WHITE.

PACKAGING:
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm). OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY D.PARHAM CHECKED BY T.CLAIRE APPROVED BY R.CARRICK	03/01/2002 11/08/2001 03/01/2002	
ALL OTHER DIMENSIONAL TOLERANCES: .XX = ± .02 [5] FRACTIONS ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION ADPT, SKT SAVER HD44 SLIM M/F
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE B CAGE CODE 43321 SCALE: NONE	ITEM NO. DGBH44MF CAD FILE: DGBH44MF.3LDRAW SHEET 1 OF 1