THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

D

	REVISIONS					
REV	DESCRIPTION		APPROVED			
Α	A DRAWING REPLACES FOA-321-OD1 9/24/14 D. CASTRO		D. CASTRO			
В	ECN 7689: FOA-MPOFB WAS FOA-012	12/9/14	D. CASTRO			
С	C ECN 10609 SLEEVE MATERIAL FROM BRONZE TO CERAMIC 08/18/20					



## FIBER OPTIC ADAPTOR KIT

KIT CONTENTS						
PART #	PART # DESCRIPTION					
FOA-201	ADAPTOR; ST-SC; SIMPLEX; CERAMIC ALIGNMENT SLEEVE	1				
FOA-301	ADAPTOR; ST-FC; SIMPLEX; CERAMIC ALIGNMENT SLEEVE	1				
FOA-302	ADAPTOR; SC-FC; SIMPLEX; CERAMIC ALIGNMENT SLEEVE	1				
FOA-001	ADAPTOR; ST-ST; SIMPLEX; CERAMIC ALIGNMENT SLEEVE	1				
FOA-002	ADAPTOR; SC-SC; SIMPLEX; CERAMIC ALIGNMENT SLEEVE	1				
FOA-003	ADAPTOR; FC-FC; SIMPLEX; CERAMIC ALIGNMENT SLEEVE	1				
FOA-004	ADAPTOR; SMA906-SMA906; SIMPLEX	1				
FOA-500A	ADAPTOR; LC-LC; SIMPLEX; CERAMIC ALIGNMENT SLEEVE	1				
FOA-701	ADAPTOR; MU-MU; SIMPLEX	1				
FOA-600 ADAPTOR; MTRJ-MTRJ; DUPLEX		1				
FOA-MPOFB	MPO COUPLER W/ FLANGE, BLACK KEYWAY CONVERTIBLE	1				



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS	DATE	50 High Street, West Mill, North Andover, MA 01845 USA.			
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0		DRAWN BY C.MCCORMICK	07/03/2003	Phone: 1.800.341.5266 1.978.682.6936			
	>12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0	D.PARHAM	07/10/2003	CATEGORY			
	>120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	APPROVED BY R. C.A.RRIC K	07/10/2003	FIBER OPTIC			
ALL OTHER DIMENSIONAL TOLERANCES:  .X = ± .2 [5] FRACTIONS  .XX = ± .02 [.5] ± 1/32		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES		PRODUCT DESCRIPTION			
	$.XXX = \pm .005 [.13]$ ANGLES $\pm 1^{\circ}$	MAY VARY		ADPTR KIT, SC ST FC COUPLERS			
	THIRD-ANGLE PROJECTION	COLOR VARIATIONS MAY OCCUR		A 43321 DWG. NO. FOA-321			
	9)			SCALE: NONE CAD FILE: FOA-321.SLDDRW SHEET 1 OF 1			
	<b>↑</b>						