


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/30/10	D.GRIFFIN


DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
INSULATOR	TEFLON	WHITE
BRAID HOLDER	BRASS	NICKEL PLATE
CONTACT PIN	BRASS	GOLD PLATE
FERRULE	COPPER	NICKEL PLATE




FERRULE




CONTACT PIN
(SOLDER TYPE)



BODY



FERRULE CRIMP SIZE



RECOMMENDED
CABLE STRIPPING

NOTES:

ELECTRICAL:
 IMPEDANCE: 50 OHM
 FREQUENCY RANGE: DC ~ 4 GHz (USEABLE TO 10 GHz)
 VSWR: 1.2 MAX. @ DC ~ 4 GHz
 DIELECTRIC WITHSTANDING VOLTAGE: 1,000 Vrms
 DURABILITY: 500 CYCLES MIN.

MISCELLANEOUS:
 APPLICATIONS: LMR100, RG174/U, RG188A/U, RG316/U.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS D.FRISIELLO CHECKED BY K.BURGNER APPROVED BY K.BURGNER	DATE 9/27/10 9/27/10 9/27/10	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321 DWG. NO. ASMBJ-1100
SCALE: NONE		CAD FILE: ASMBJ-1100.SLDDRW	REV. A SHEET 1 OF 1