


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 5294: REDRAWN PER NEW SUPPLIER SPEC.	2/8/11	D. CASTRO
C	ECN 8873 UPDATE PER NEW VENDOR SPEC	07/31/17	B.PUCHASKI

DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL
DIELECTRIC	PTFE	NATURAL
CENTER PIN	BRASS	GOLD
FERRULE	BRASS	NICKEL
PRESS FIT WASHER	BRASS	NICKEL



**NOTES:**

**ELECTRICAL:**  
 IMPEDANCE: 50 OHMS  
 WITHSTAND VOLTAGE: 1500V  
 FREQUENCY RANGE: 0~6 GHz  
 VSWR: <1.50 @ 0~6 GHz  
 DURABILITY: > 500 CYCLE  
 CABLE RETENTION: > 40 POUNDS

**MISCELLANEOUS:**  
 COMPONENTS SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATIONS PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY M. AUDUS CHECKED BY M. AUDUS APPROVED BY P. PESA	DATE 10/26/06 10/26/07 10/26/06	50 HIGH STREET NORTH ANDOVER, MA 01845		
	CATEGORY COAXIAL				
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION CON, TNC FEMALE CRIMP LMR240		
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>ATF-1506</b>
		SCALE: NONE	CAD FILE: ATF-1506.SLDDRW		SHEET 1 OF 1