

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

DESCRIPTION	MATERIAL	FINISH	
BODY	BRASS	NICKEL	
PIN	BRASS	GOLD	
INSULATION	PTFE	-	
SHELL	BRASS	NICKEL	
FERRULE	BRASS	NICKEL	
PF FERRULE STUD	BRASS	NICKEL	
GROUND RING	BRASS	NICKEL	
RETAINING RING	BRASS	NICKEL	
GASKET	SILICONE RUBBER	ORANGE	
NUT	BRASS	NICKFI	

	REVISIONS					
REV	DESCRIPTION	DATE	APPROVAL			
С	ECN 4601: REVISE CRIMPING DIMENSIONS, NEW FORMAT	3/10/10	D.FRISIELLO			



RECOMMENDED CABLE STRIPPING DIMENSIONS



## MISCELLANEOUS:

NOTES:

**ELECTRICAL:** 

COMPONENTS SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATIONS PS-0031.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

## **RoHS Compliant** ✓

	APPROVALS	DATE	1				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	DRAWN BY K.BURGNER	11/26/07	Ŀ	CO			BEECHWOOD DRIVE DRTH ANDOVER, MA
OVERALL CABLE LENGTH TOLERANC ≤12 [305] = +1 [25] / -0	E: CHECKED BY K.BURGNER	11/26/07	CATEGO	)BA		THICCOIVIC Y	01845
>12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120[3048] - 300[7620] = +6 [152] / -0	APPROVED BY K.BURGNER	11/26/07	CAILGO	7K I	C	OAXIAL	
>300[7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANC	ES: CONFIGURATION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		T DESCRIPTION	DIAD DIC	SUT ANGLE	CONNECTOR
.X = .2 .XX = .02 .XXX = .005				N-MALE CRIMP RIGHT ANGLE CONNECTOR 240 SERIES CABLE			
PROJECTION (+)	COLOR VARI MAY OCC		SIZE	FSCM NO. 43321	DWG. NO.	ANM-1516	S REV.
			SCALE	: NONE CAD	FILE: ANM-1516	S.SLDDRW	SHEET 1 OF 1