		7		6		5			3	5		2 REVISIONS		1	
OPER	ORMATION CONTAINED IN RTY OF L-COM, INC. ANY REF JT THE WRITTEN PERMISSION C	PRODUCTION IN PAR	T OR WHOLE						REV		DESCRIPTIC			DATE	APPRO
ΉΟι	JT THE WRITTEN PERMISSION C	of L-COM, INC. IS PR	CHIBITED.						H ECN 3	139: UPDATE DWG	g format			1/7/08	D.GRIFFIN
_											CABLE STRIPPING D	IMENSIONS		6/30/09	D.FRISIELI
									K ECN 7	085:UPD CONN E	MAS/PICTORALLY.	UPDATED NOTES/I	FORMAT	9/27/13	D. DESJA
	DESCRIPTION	MATERIAL	FINISH						L ECN 7	523 REMOVE INSU	JLATING COVER, U	PDATE OA.DIMS P	PER SUPPLIER DRW	/ 7/22/14	B.PUCHA
	BODY	BRASS	NICKEI	L											
	INSULATOR	PTFE	-												
	CENTER PIN	BRASS	GOLD FL/												
	FERRULE CAP	BRASS BRASS	NICKEI NICKEI												
						(1	CAP				128				
					-	.61 [15.6]					.128 [3.25]		>		
			ERRULE					.65 [16.6]	Ĺ	C	FER	.52 .52 .13.	AP SIZE		
	NOTES:					Ŵ								.06 .06	63 60
	ELECTR IMPEDI FREQU	<b>ICAL:</b> ENCE: 50 OH ENCY RANGE	MS				1/4	"-36UNS-2B			REC	COMMEN BLE STRIPF	IDED PING		L
	APPLIC	ATION: , RG188, AND		BLE ASSEN	<b>ABLIES</b>										
		<b>GING:</b> ONENT SHALL RDANCE WITH					UNLESS OTHERWIS DIMENSIONS ARE IN OVERALL CABLE LENC ≤12 (305) = +1	INCHES [mm]	APPROVALS DRAWN BY C.MCCORMICK HECKED BY	DATE 12/19/2001				45 BEECHV NORTH AN 01	
		MENSIONS AR	e for refe	RENCE ON	NLY.		OVERALL CABLE LENC \$12 [305] =+1 >12 [305] \$60 [1524] >60 [1524] \$120 [3048] >120 [3048] \$300 [762] >300 [7620] =+		D.PARHAM PPROVED BY CARRICK	12/19/2001	CATEGORY PRODUCT DESCRI		JAXIAL		
	REGULATORY COMPLIANCE: CE2011/65/EU(RoHS DIRECTIVE)						ALL OTHER DIMENSION .X = ± .2 [5 .XX = ± .02 .XXX = ±.00	AL TOLERANCES: 5.08] [.51] 5 [.13]	CONFIGURATIC UNDIMENSION MAY V	IED FEATURES	CONN	SMA M I		4 CRIN	AP NK
										ARIATIONS DCCUR 11-026	A 433	CAD FILE: BAG	BAC	02A	SHEET 1