

NOTES:

MATERIAL:

BODY: BRASS LOCK WASHER AND GROUND TAB: STEEL CONTACT: PHOSPHOR BRONZE INSULATOR: ACETAL NUT: BRASS

FINISH:

BODY: NICKEL PLATE LOCK WASHER AND GROUND TAG: NICKEL PLATE CONTACT: GOLD PLATE NUT: NICKEL PLATE

ELECTRICAL:

Α

IMPEDANCE: 50 OHM

PACKAGING:

INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG


6

-5

4

APPLICATION: PANEL MOUNT

8



	2 1	
	REVISIONS	
	REV DESCRIPTION DATE CHANGED BY	-
	A RELEASED FOR PRODUCTION 10/15/01 MCCORMICK	-
	B ECN#1605 ADDED COMPONENT SPECIFICATION TABLE 12/22/03 MCCORMICK	-
	C ECN# 2296 ADDED NOTES & REVISED COMPONENT SPECS 02/24/06 MCCORMICK D ECN 3165: UPDATE DWG FORMAT 1/21/08 D.GRIFFIN	1
		1
		D
	$\langle \Box \rangle$	
		C
	(\bigcirc)	
		-
		В
	\wedge	
	LOCKWASHER	
	HEX NUT	
	GROUND TAG	
	-	
		_
	L-COM 45 BEECHWOOD DRIVE	- A
n	nliant V	
	PRODUCTS 01845	4
m]	DRAWN BY CATEGORY COAXIAL	
2°	C.MCCORMICK 10/15/2001	-
	CHECKED BY PRODUCT DESCRIPTION D.PARHAM 10/15/2001	
	APPROVED BY RECEPTACLE BNC JACK BHD	
	R.CARRICK 10/15/2001 SIZE FSCM NO. DWG. NO. REV.	1
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES B 43321 BAC70A D	
	MAY VARY	4
	SCALE: 1:1 CAD FILE: BAC70A.SLDDRW SHEET 1 OF 1	
	<u>~</u>	