



## NOTES:

- 1. PROFFESIONAL GRADE HEAVY DUTY RATCHETING CRIMP TOOL FOR MODULAR PLUGS - RJ22, RJ11, RJ12, RJ45, OR 10-PIN.
- 2. FULLY RATCHETING CRIMP ACTION ASSURES THAT EACH CRIMP IS COMPLETED CORRECTLY.
- 3. BUILT IN WIRE CUTTER MAKES FOR FASTER CABLE PREP WITH JUST ONE TOOL.
- 4. ALL STEEL CONSTRUCTION WITH PLASTIC HANDLE GRIPS FOR OVERALL COMFORT.
- 5. (2X) LOCKING SCREWS ARE SUPPLIED WITH DIE SETS.
- 6. HARDENED DIES (SOLD SEPERATELY AND SHOWN ONLY FOR CLARITY) PROVIDE FOR A LONG SERVICE LIFE AND QUALITY CONNECTIONS.
- 7. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

	UNLESS OTHERWISE SPECIFIED,	APPROVALS	DATE	1_0		W	Global		H STREET	
	DIMENSIONS ARE IN INCHES [mm]	DRAWN BY	00/07/00/0		کا ت	<b>炉 -  </b>	Connec	NORTH AN	- ,	MA
	OVERALL CABLE LENGTH TOLERANCE:	DFRISIELLO	08/27/2012				Connec	018	845	
	=12 [000] - 11 [20] / 0	D.DES.IARDIN	08/27/2012	CATEGOR	Y					
	>60 [1524] <120 [3048] = +4 [102] / -0	APPROVED BY	00/2//2012	TELECOM/MODULAR						
	>120 [3048] <300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES:	D.GALLAGHER	08/27/2012	ILLLCOM/MODULAR						
			PRODUCT DESCRIPTION							
	X = ± .2 [5.08]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CRIMP TOOL, FRAME ONLY						
		COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	433		DWG. NO.	HTS7100		REV.
				SCALE: 1	NONE	CAD FI	LE: HTS7100.SLI	DDRW	SHEET 1 (	OF 1
_	Α								•	

8