

**Bulk Cable Specification**

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH	SPLICES (MAX)
RG316-100	COIL	LOGO BAG	100 FT.	-
RG316-500	SPOOL	STRETCH WRAP	500 FT.	MAY HAVE 1
RG316-1K	SPOOL	STRETCH WRAP	1,000 FT.	MAY HAVE 2
RG316-PROD	-	-	-	MAY HAVE 2



50 OHM IMPEDANCE.

CENTER CONDUCTOR: 26 AWG. (7X.0067) SILVER COATED  
COPPER COVERED STEEL.

SHIELDING: SILVER COATED COPPER BRAID (95% COVERAGE).

INSULATION: TFE TEFLON.

JACKET: BROWN FEP.

OPERATING TEMPERATURE: -70°C - +200°C VW-1

VERTICAL FLAME TEST COMPLIANT

NOMINAL ATTENUATION		
MHz	Db/100ft	Db/100m
50	5.6	18.4
100	8.3	27.2
200	12.0	39.4
400	17.5	57.4
1,000	29.0	95.1

NOTE:

SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC