


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/16/05	MCCORMICK



NOTES:

1.0 TEST:

1.1 INSERTION LOSS TESTED AT 1300nm WITH A <-1.0 dB RESULT.

2.0 PACKAGING:

2.1 THE PRODUCT SHALL BE PRESERVED & PACKAGED IN A MANNER WHICH WILL AFFORD ADEQUATE PROTECTION AGAINST CORROSION, DETERIORATION, AND PHYSICAL DAMAGE DURING SHIPMENT.

2.2 INDIVIDUALLY PACKAGE EACH ASSEMBLY UTILIZING APPROPRIATE SIZED BAG DEPICTED ON [1AN01-001-OD1](#) . MARK EACH BAG PER [LSP-010](#).

3.0 WORKMANSHIP:

3.1 CABLE ASSEMBLIES SHALL BE MANUFACTURED IN SUCH A MANNER AS TO BE UNIFORM IN QUALITY AND SHALL BE FREE FROM DEFECTS THAT WILL ADVERSELY AFFECT LIFE, SERVICEABILITY, OR APPEARANCE.

4.0 VISUAL AND MECHANICAL:

4.1. CABLE ASSEMBLIES SHALL BE INSPECTED TO VERIFY COMPLIANCE TO THIS DRAWING.

5.0 MANUFACTURING:

5.1 CABLE ASSEMBLY UTILIZES "PC" POLISH TYPE.

PART NUMBER	LENGTH METER
FODST-10G-01	1.0
FODST-10G-02	2.0
FODST-10G-03	3.0
FODST-10G-04	4.0
FODST-10G-05	5.0

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
X ±.1
XX ±.05
XXX ±.005
CABLE LENGTH TOLERANCE
≤300' ±5% >300' ±2%

APPROVALS	DATE
DRAWN BY C.MCCORMICK	12/16/2005
CHECKED BY M.LAHEY	12/16/2005
APPROVED BY D.PARHAM	12/16/2005

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION			
ST TO ST 50/125 DUPLEX 10 GIG			
DRAWING TITLE			
OUTLINE DRAWING			
SIZE A	FSCM NO. 43321	DWG. NO. FODST-10G-01-OD1	REV. A
SCALE: NONE		CAD FILE: FODST-10G-01-OD1.SLDDRW	SHEET 1 OF 1