



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/16/16	D.GRIFFIN



PART NUMBER	LENGTH	
	FEET	METERS
TRG502-T4T-05M	1.64	0.5
TRG502-T4T-1M	3.28	1.0
TRG502-T4T-2M	6.56	2.0
TRG502-T4T-3M	9.84	3.0
TRG502-T4T-5M	16.41	5.0
TRG502-T4T-10M	32.82	10.0

**NOTES**

**MATERIAL:**  
 MOLDED HOOD: THERMOPLASTIC POLYURETHANE, BLACK  
 INSULATOR: NYLON, BLACK  
 SHELL/SCREW NUT: BRASS, NICKEL PLATE  
 CONTACTS: PHOSPHOR BRONZE, 15µ" MIN. GOLD PLATE

**ELECTRICAL:**  
 NOMINAL VOLTAGE RATING: 250 VAC/VDC  
 MAX CURRENT: 4A

**APPLICATION:**  
 INGRESS PROTECTION RATING IS IP68 (MATED).

**ENVIRONMENTAL:**  
 OPERATING TEMPERATURE RANGE: -40°C TO +80°C  
 CABLE JACKET RESISTANCE: OIL, SUNLIGHT, AND WELD SPLATTER RESISTANT

**MISCELLANEOUS**  
 CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS DRAWN BY: D.CUI CHECKED BY: D. DESJARDIN APPROVED BY: D. GUTS DAURO	DATE 01/05/16 03/10/16 03/10/16	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY <b>TELECOM/MODULAR</b>		
	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION <b>C5E M12D M/F TPE 24 TEL</b>		
	PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>TRG502-T4T</b>