


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/25/2010	D.GRIFFIN
B	ECN 4691: ADDED M12 CONNECTOR CALL-OUT	04/16/2010	DFP
C	ECN 6206: ADDED "A-CODED" FOR CLARIFICATION	06/01/2012	DFRISIELLO
D	ECN 9483: ADD -10 METER LENGTH TO CHART	10/29/2018	DFRISIELLO



WIRING MAP		
P1	COLOR	J1
1	BROWN	1
2	WHITE	2
3	BLUE	3
4	BLACK	4
5	GREEN	5

PART NUMBER	LENGTH	
	FEET	METERS
M12M12F5A-0.5	1.64	0.5
M12M12F5A-1	3.28	1
M12M12F5A-2	6.56	2
M12M12F5A-3	9.84	3
M12M12F5A-5	16.41	5
M12M12F5A-10	32.81	10



NOTES:

1. WATERPROOF RATING: IP68.
2. MOLDED HOOD: POLYURETHANE, BLACK.
3. SCREW NUT: ZINC ALLOY, NICKEL PLATED.
4. PINS: COPPER ALLOY, GOLD PLATED.
5. CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLY BAG PER L-COM SPECIFICATION PS-0031.
6. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
7. CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY D.PARHAM CHECKED BY P.MCNEIL APPROVED BY D.CASTRO	DATE 01/22/2010 01/25/2010 01/25/2010	50 HIGH STREET NORTH ANDOVER, MA 01845				
	CATEGORY TELECOM/MODULAR			PRODUCT DESCRIPTION CA M12 TO M12 F 5 POS A			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. M12M12F5A
	SCALE: NONE		CAD FILE: M12M12F5A.SLDDRW		SHEET 1 OF 1		