


Assorted D-Sub Adapter Selection Matrix

Use this handy chart to locate the desired D-Sub adapter. Simply locate the connector sizes and genders along the top and intersect with the row showing the desired adapter style. If a specific adapter is not listed, please visit our website at www.L-com.com for the latest information and select the Product

Finder on the left side of the screen or call our Technical Support Group at 800-343-1455 for assistance. Wiring schemes are listed near each adapter in the catalog or on the engineering drawing available on L-com's website.

ASSORTED D-SUB ADAPTER SELECTOR GUIDE									
ADAPTER TYPE	INTERFACE	DB9 MALE-DB25 FEMALE	DB9 FEMALE-DB25 MALE	DB9 FEMALE-DB25 FEMALE	DB9 MALE-DB9 FEMALE	DB25 MALE-DB25 FEMALE	DB9 FEMALE-HD15 MALE	DB9 MALE-HD15 MALE	
	AT MODEM	DG259FM-IBM DMA010MF	DG259MF-IBM DGL259MF-IBM DMA010FM	DGL259FF-IBM					
	NULL MODEM				DMA060MF	DMA070MF DMA071MF DMA072MF DMA074MF			
	REVERSER (Position 2 & 3)				DMA030MF	DMA040MF			
RGB MONITOR						DMB510MF DMB512MF	DMB510MM DMA100MM		










Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

RoHS Slim-Line DB9 or DB25 Null Modems, Adapters and Reversers - Communicate Without Modems

L-com's series of Null Modems and Reversers are completely shielded. More important, their extremely low profile reduces leverage strain and breakage on overstressed computer ports. The Null Modems shown are typical of our Slim-Line manufacturing technique. They are also available in virtually any wiring configuration. OEM users are requested to send wiring data for our consideration.

DMA030MF	Slim-Line Reversing Adapter, Pins 2 and 3, DB9 Male / Female	5.95	5.36	4.76	4.17	3.57
DMA040MF	Slim-Line Reversing Adapter, Pins 2 and 3, DB25 Male / Female	6.95	6.25	5.56	4.87	4.17
DMA060MF	Slim-Line Null Modem Adapter, DB9 Male / Female	5.95	5.36	4.76	4.17	3.57
DMA070MF	Slim-Line Null Modem Adapter, DB25 Std. Handshake, Male / Female	6.95	6.25	5.56	4.87	4.17
DMA071MF	Slim-Line Null Modem Adapter, DB25 Full Handshake, Male / Female	6.95	6.25	5.56	4.87	4.17
DMA072MF	Slim-Line Null Modem Adapter, DB25 Auto Handshake, Male / Female	6.95	6.25	5.56	4.87	4.17
DMA074MF	Slim-Line Null Modem Adapter, DB25 Specialty, Male / Female	6.95	6.25	5.56	4.87	4.17



Gender Changer and Socket Saver Selection Matrix

Use this handy chart to locate the desired gender changer or socket saver. Simply locate the connector size along the top (standard or filtered) and intersect with the row showing the desired connector genders. If a specific

adapter is not listed, please visit our website at www.L-com.com for the latest information and select the Product Finder on the left side of the screen or call our Technical Support Group at 800-343-1455 for assistance.

GENDER CHANGER & SOCKET SAVER D-SUB ADAPTER SELECTOR GUIDE (ALL WIRING STRAIGHT THROUGH)															
INTERFACE	STANDARD D-SUB								HIGH DENSITY D-SUB						
	9 PIN D-SUB	9 PIN D-SUB FILTERED	15 PIN D-SUB	15 PIN D-SUB FILTERED	25 PIN D-SUB	25 PIN D-SUB FILTERED	37 PIN D-SUB	37 PIN D-SUB FILTERED	50 PIN D-SUB	15 PIN HIGH DENSITY	26 PIN HIGH DENSITY	44 PIN HIGH DENSITY	62 PIN HIGH DENSITY	78 PIN HIGH DENSITY	
GENDER	FEMALE-FEMALE	DGB9F		DGB15F		DGB25F		DGB37F		DGB50F	DGBH15F DGBV15F* DMB521F	DGBH26F	DGBH44F	DGBH62F	DGBH78F
	MALE-MALE	DGB9M		DGB15M		DGB25M		DGB37M		DGB50M	DGBH15M DGBV15M* DMB520M	DGBH26M	DGBH44M	DGBH62M	DGBH78M
	MALE-FEMALE	DGB9MF DG909MF1 DG909MF2	DGF9MF DGF9MF	DGB15MF	DGF15MF DGF15MF	DG9025MF1 DG9025MF2 DGB25MF	DGF25MF DGF25MF	DGB37MF	DGF37MF DGF37MF	DGB50MF	DGBH15MF1 DG90H15MF1 DG90H15MF2 DGBV15MF*	DGBH26MF	DGBH44MF	DGBH62MF	DGBH78MF

*Pin 9 missing for older, legacy VGA applications.