

Bulk Cable Specification

MODEL	PRIMARY PACKAGING	SECONDARY PACKAGING	LENGTH
RG142B-100	COIL	BOX	100 FT.
RG142B-500	SPOOL	STRETCH WRAP	500 FT.
RG142B-1K	SPOOL	STRETCH WRAP	1000 FT.



50 OHM IMPEDANCE.

CENTER CONDUCTOR: 18 AWG. SOLID SILVER COATED COPPER.

SHIELDING: 2 SILVER COATED COPPER BRAIDS (96% COVERAGE).

INSULATION: TFE TEFLON.

JACKET: BROWN FEP.

OPERATING TEMPERATURE: -70°C - +200°C VW-1
VERTICAL FLAME TEST COMPLIANT.

NOMINAL ATTENUATION		
MHz	Db/100ft	Db/100m
50	2.7	8.9
100	3.9	12.8
200	5.6	18.4
400	8.2	26.9
1,000	13.5	44.3

NOTE:

1. SEE ASSEMBLY INSTRUCTIONS ASI-0026.DOC
2. MAY CONTAIN MORE THAN ONE PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25 FEET.