


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/28/11	D.GRIFFIN



NOTES:  
 50 OHM, 1/4 WATT TERMINATION  
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.  
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**RoHS Compliant** ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ .XX = $\pm .02$ .XXX = $\pm .005$	APPROVALS DRAWN BY D.FRISIELLO	DATE 10/27/11		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	CHECKED BY D.PARHAM APPROVED BY P.PESA	DATE 10/27/11 10/27/11		CATEGORY COAXIAL			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION CAP, 50 OHM TERM TNC W/ CHAIN	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. USP-CTT50	REV. <b>A</b>
SCALE: NONE			CAD FILE: USP-CTT50.SLDDRW		SHEET 1 OF 1		