

Item #	Description	1-9	10-24	25-99	100-249	250-499
✓RoHS	Stranded Conductor Modular Plugs - Rectangular Entry for Flat Cable					
A full complement of modular plugs is offered for all applications. Piercing-type connections are simultaneously made through each stranded conductor of 24-28 AWG flat modular cable. 15 microinches gold plating on contacts. Sold in packages of 100 plugs.						
TD4P4HS	Modular Plugs, Handset (4x4), Pkg/100	19.95	18.35	16.76	15.16	13.57
TD6P4C	Modular Plugs, RJ11 (6x4), Pkg/100	19.95	18.35	16.76	15.16	13.57
TD6P6C	Modular Plugs, RJ12 (6x6), Pkg/100	24.95	22.95	20.96	18.96	16.97
TD6P6MMJ	Modular Plugs, MMJ (6x6), Pkg/100	29.95	27.55	25.16	22.76	CALL
TD8P8C	Modular Plugs, RJ45 (8x8), Pkg/100	39.95	36.75	33.56	30.36	27.17
TD8P8CK	Modular Plugs, RJ45 (8x8) (Keyed), Pkg/100	39.95	36.75	33.56	30.36	27.17

✓RoHS Stranded Conductor Modular Plugs - Radiused Entry for Round or Flat Cable

These modular plugs have a radiused rear entry compatible with most round and flat cables. 50 microinches gold plating on contacts. Compatible with 24-28 AWG stranded conductors.

TDR6P4C	Modular Plugs, RJ11 (6x4), Pkg/100	19.95	18.35	16.76	15.16	CALL
TDR6P6C	Modular Plugs, RJ12 (6x6), Pkg/100	24.95	22.95	20.96	18.96	CALL
TDR8P8C	Modular Plugs, RJ45 (8x8), Pkg/100	39.95	36.75	33.56	30.36	CALL
TDR10P10C	Modular Plugs, RJ45 (10x10), Pkg/100	49.95	45.95	41.96	37.96	CALL

✓RoHS Shielded Long Body RJ45 Generic Plug

This plug will accept round or flat cable with solid or stranded wires. Prices shown are per piece. Compatible with generic 8x8 crimp tools such as L-com part numbers: HT210A, HT1500, HTS7100 + HTS7100-08A die set and HTS2100 + HTS2100-08 die set.



TB8PCSR	Shielded Modular Plug, RJ45 (8x8), Single	0.95	0.87	0.80	0.72	CALL
-------------------------	---	------	------	------	------	------

✓RoHS Shielded Category 5E and Category 6 RJ45s for Solid or Stranded Cables

A superior high performance shielded plug system that allows users to perform factory grade terminations in the field is now available. A unique metallic strain relief provides superior cable retention and a reliable 360 degree shielding contact. The short body design combined with a loading bar allows easy insertion while maintaining Category 5E or Category 6 twist requirements. Superior two-point contact design is compatible with solid and stranded cable. Improve your shielded cable performance by designing in L-com's shielded plugs.

TDS8PC5	Category 5E Shielded Modular Plug, RJ45 (8x8), - Pkg/50	74.50	71.52	68.54	65.56	62.58
TDS8PC6	Category 6 Shielded Modular Plug, RJ45 (8x8), - Pkg/50	79.95	76.75	73.55	70.36	67.16
TDS8CVR-GR	8x8 Shielded Covers, Gray - Pkg/50	12.50	11.50	10.50	9.50	CALL
TDS8CVR-BK	8x8 Shielded Covers, Black - Pkg/50	12.50	11.50	10.50	9.50	CALL
TDS8CVR-BL	8x8 Shielded Covers, Blue - Pkg/50	12.50	11.50	10.50	9.50	CALL
TDS8CVR-GN	8x8 Shielded Covers, Green - Pkg/50	12.50	11.50	10.50	9.50	CALL
TDS8CVR-IV	8x8 Shielded Covers, Ivory - Pkg/50	12.50	11.50	10.50	9.50	CALL
TDS8CVR-RD	8x8 Shielded Covers, Red - Pkg/50	12.50	11.50	10.50	9.50	CALL
TDS8CVR-WH	8x8 Shielded Covers, White - Pkg/50	12.50	11.50	10.50 <td 9.50	CALL	
TDS8CVR-YL	8x8 Shielded Covers, Yellow - Pkg/50	12.50	11.50	10.50	9.50	CALL
HTS2500	Crimp Tool for Shielded Plugs with Strain Relief, One Step	69.50	66.72	63.94	61.16	CALL
HTS2600	Crimp Tool for Shielded Plugs with Strain Relief, Two Step	79.50	76.32	73.14	69.96	CALL

Standard Alignment



How to assemble a TDS8PC5 and TDS8PC6 series shielded Category 5E and Category 6 modular plugs

STEP 1

Strip jacketing and shield to dimensions shown.

STEP 2

Fold shield back onto jacketing. Wrap drain wire one and a half times around shield. Trim excess.

STEP 3

Untwist pairs and arrange to desired order. Trim conductors at an angle and insert into loading bar. Trim excess wires.

STEP 4

Insert prepared cable into plug.

STEP 5

Bend strain relief to lay along cable.

STEP 6

Crimp plug with the specially designed HTS2500 or HTS2600 crimp tool.

See The Video
www.L-com.com/Videos/A22

How to terminate a TDS8PC modular plug
 See the free video tip and more at L-com.com/Videos/A22