



"STYLE" refers to shape of antenna in series.

Item #	Style	Description	1-9	10-24	25-99	100-249	250-499
--------	-------	-------------	-----	-------	-------	---------	---------

### HyperLink™ Patch and Panel Antennas - Compact and Lightweight

These high performance directional patch and panel antennas are available for indoor and outdoor applications covering multiple popular frequencies. Our patch antennas are lightweight and feature aesthetic UV-stable, UL flame rated plastic radomes which can also be painted to match the room or building structure. Designed to be installed for horizontal or vertical polarization, they can be wall or ceiling mounted, as well as mast mounted using U-bolts. Designed specifically as cost-effective solutions for today's demanding wireless applications, HyperLink™ patch and panel antenna products offer a unique combination of superior all-weather performance, durability and aesthetics. Applications include IEEE 802.11b/g/n, 900 MHz cellular, RFID, 802.16, 802.20 and WiMAX.

- Point-to-point systems
- Easy to install
- RoHS compliant
- Public wireless hotspot
- Point-to-multipoint systems
- Indoor and outdoor models available

#### Mast Mounting:

L-com's patch antennas offer several unique mounting options. They can be mounted flat against a wall, or to a mast using a pair of 2 inch U-bolts. The antennas also accept most tilt-and-swivel security camera brackets equipped with standard 1/4-20 threads.



HG2414P - Rear view



HG2408P-NF - Rear view

#### Flush Mount:

The HG2408P-NF can be mounted flat against the wall or ceiling. Its unique design allows the cable to exit out of the side or from the back of the unit which is ideal for mounting in locations that require the cable to be hidden.

### HyperLink™ Patch and Panel Antennas - Compact and Lightweight

These are low cost high gain antennas that come with their own enclosure space within the antenna radome. Mount your wireless card radio behind the antenna and seal the radome. All come with quick connect CAT5/6 connections. Antenna pigtail cable options are RP-SMA Plug, RP-TNC Plug, MMCX and UFL (with others available).

#### ✓RoHS HyperLink™ Family of 2.4 GHz, 3.5 GHz and 5.1-5.8 GHz Panel Enclosure Antennas

HG2414PEV	J	2.4 GHz 14 dBi Panel Enclosure Antenna	44.99	43.19	41.39	39.59	37.79
HG2414PEV-MMCX	J	2.4 GHz 14 dBi Panel Enclosure Antenna, MMCX Antenna Cable	49.99	47.99	45.99	43.99	41.99
HG2414PEV-RSP	J	2.4 GHz 14 dBi Panel Enclosure Antenna, RP-SMA Plug Antenna Cable	49.99	47.99	45.99	43.99	41.99
HG2414PEV-RTP	J	2.4 GHz 14 dBi Panel Enclosure Antenna, RP-TNC Plug Antenna Cable	49.99	47.99	45.99	43.99	41.99
HG2414PEV-UFL	J	2.4 GHz 14 dBi Panel Enclosure Antenna, UFL Antenna Cable	49.99	47.99	45.99	43.99	41.99
HG3514PEV	J	3.5 GHz 14 dBi Panel Enclosure Antenna	49.99	47.99	45.99	43.99	41.99
HG3514PEV-MMCX	J	3.5 GHz 14 dBi Panel Enclosure Antenna, MMCX Antenna Cable	54.99	52.79	50.59	48.39	46.19
HG3514PEV-RSP	J	3.5 GHz 14 dBi Panel Enclosure Antenna, RP-SMA Plug Antenna Cable	54.99	52.79	50.59	48.39	46.19
HG3514PEV-RTP	J	3.5 GHz 14 dBi Panel Enclosure Antenna, RP-TNC Plug Antenna Cable	54.99	52.79	50.59	48.39	46.19
HG3514PEV-UFL	J	3.5 GHz 14 dBi Panel Enclosure Antenna, UFL Antenna Cable	54.99	52.79	50.59	48.39	46.19
HG5158PEV	J	5.1 GHz to 5.8 GHz 18 dBi Panel Enclosure Antenna	54.99	52.79	50.59	48.39	46.19
HG5158PEV-MMCX	J	5.1 GHz to 5.8 GHz 18 dBi Panel Enclosure Antenna, MMCX Antenna Cable	59.99	57.59	55.19	52.79	50.39
HG5158PEV-RSP	J	5.1 GHz to 5.8 GHz 18 dBi Panel Enclosure Antenna, RP-SMA Plug Antenna Cable	59.99	57.59	55.19	52.79	50.39
HG5158PEV-RTP	J	5.1 GHz to 5.8 GHz 18 dBi Panel Enclosure Antenna, RP-TNC Plug Antenna Cable	59.99	57.59	55.19	52.79	50.39
HG5158PEV-UFL	J	5.1 GHz to 5.8 GHz 18 dBi Panel Enclosure Antenna, UFL Antenna Cable	59.99	57.59	55.19	52.79	50.39

#### ✓RoHS 900 MHz Patch Antennas

HG908P-NF	A	8 dBi, 8in (20.3cm) Sq., 12in (30.5cm) Pigtail with N Female Connector	44.99	40.49	35.99	31.49	26.99
HG908P-SM	A	8 dBi, 8in (20.3cm) Sq., 12in (30.5cm) Pigtail with SMA Male Connector	54.99	49.49	43.99	38.49	32.99

#### ✓RoHS 1.9 GHz Patch Antennas

HG1908P-NF	A	8 dBi, 4in (10.2cm) Sq., 12in (30.5cm) Pigtail with N Female Connector	39.99	35.99	31.99	27.99	23.99
HG1912P-NF	A	12 dBi, 8in (20.3cm) Sq., 12in (30.5cm) Pigtail with N Female Connector	49.99	48.49	46.99	45.49	CALL

#### ✓RoHS 2.4 GHz Patch Antennas

HG2408P-NF	C	8 dBi, 4in (10.2cm) Round, 12in (30.5cm) Pigtail with N Female Connector	24.99	22.49	19.99	17.49	14.99
HG2409PCL-NF	A	8 dBi, 4in (10.2cm) Sq., LH Cir Polarized, 12in (30.5cm) Pigtail with N Female Con.	14.99	13.79	12.59	11.39	10.19
HG2409PCR-NF	A	8 dBi, 4in (10.2cm) Sq., RH Cir Polarized, 12in (30.5cm) Pigtail with N Female Con.	28.99	26.09	23.19	20.29	17.39
HG2409P-NF	A	8 dBi, 4in (10.2cm) Sq., 12in (30.5cm) Pigtail with N Female Connector	28.99	26.09	23.19	20.29	17.39
HG2412P	B	12 dBi, 4in (10.2cm) Sq., Integral N Female Connector	25.99	23.91	21.83	19.75	17.67
HG2414P	A	14 dBi, 8in (20.3cm) Sq., Integral N Female Connector	36.99	34.03	31.07	28.11	25.15
HG2414P-NF	A	14 dBi, 8in (20.3cm) Sq., 12in (30.5cm) Pigtail with N Female Connector	32.99	31.01	29.03	27.05	25.07
HG2416P	A	15.5 dBi, 8in (20.3cm) Sq., Integral N Female Connector	47.99	44.15	40.31	36.47	32.63
HG2418P	D	18 dBi, 12in (30.5cm) Pigtail with N Female Connector	52.99	50.34	47.69	45.04	CALL
HG2458-09P	A	9 dBi, 8in (20.3cm) Sq., Multi-Band, Integral N Female Connector	69.99	64.39	58.79	53.19	47.59

#### ✓RoHS 2.4 GHz Dual Polarized Mini Panel Antenna

This very compact panel 2.4 GHz multiple-input and multiple-output (MIMO) patch antenna is designed to operate with many manufacturers' enterprise-class 802.11n MIMO access points (APs). The antenna features two integrated 2.4 GHz patch antennas in one enclosure, making it an ideal and aesthetically pleasing antenna to support demanding indoor or outdoor applications in next generation IEEE 802.11n wireless communication systems.

HG2410DP	B	10 dBi, Dual Polarized Mini Panel with N Female Connector	29.99	27.59	25.19	22.79	20.39
----------	---	---	-------	-------	-------	-------	-------

Call for special connectors and cable lengths

