


### Super Thin SVGA is Ideal for Tight Fitting Spaces

The Super Thin SVGA series offers comparable performance of standard size SVGA assemblies in a much more compact size. Not only is the cable diameter greatly reduced but the depth of the HD15 backshell is also much more shallow than the backshells found on most SVGA assemblies. This results in a SVGA assembly that can be used in tight confines where a standard size SVGA assembly would be difficult if not impossible to use.

An additional feature of this series is reversible hardware allowing either panel mount using standoffs or traditional thumbscrews. The combined results of these features is a product series that is both compact and versatile. These features can be utilized to solve many difficult installation problems without sacrificing performance.

The Super Thin small profile construction is also utilized on our SVGA with disconnect series and our low profile KVM cables.

**Note:** All dimensions are for reference only.





Ultra Flexible

### Reversible Hardware

Detail of female end being panel mounted using standoffs

Detail of male end being mounted using thumbscrews



Item #	Description	#Coax	1-9	10-24	25-99	100-249	250-499
--------	-------------	-------	-----	-------	-------	---------	---------

### ✓RoHS Super Thin SVGA Cables with 3 Mini Coaxial Lines - HD15M to HD15M or HD15F

Utilize a revolutionary cable made with 3 ultra thin coaxial lines and still measures less than .23" in diameter. Another unique feature is user defined mounting hardware. Each cable end is capable of being connected with either male jack screws or hex standoffs with the supplied hardware! Color: Black.

CTL3VGAMM-5T	Super Thin SVGA Cable, HD15 Male / Male, 5.0ft (1.5m)	3	30.00	28.20	26.40	24.60	22.80
CTL3VGAMM-10T	Super Thin SVGA Cable, HD15 Male / Male, 10.0ft (3.0m)	3	37.50	35.25	33.00	30.75	28.50
CTL3VGAMM-15T	Super Thin SVGA Cable, HD15 Male / Male, 15.0ft (4.6m)	3	45.00	42.30	39.60	36.90	34.20
CTL3VGAMM-25T	Super Thin SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	60.00	56.40	52.80	49.20	45.60
CTL3VGAMM-50T	Super Thin SVGA Cable, HD15 Male / Male, 50.0ft (15.2m)	3	97.50	91.65	85.80	79.95	74.10
CTL3VGAMF-5T	Super Thin SVGA Cable, HD15 Male / Female, 5.0ft (1.5m)	3	30.00	28.20	26.40	24.60	22.80
CTL3VGAMF-10T	Super Thin SVGA Cable, HD15 Male / Female, 10.0ft (3.0m)	3	37.50	35.25	33.00	30.75	28.50
CTL3VGAMF-15T	Super Thin SVGA Cable, HD15 Male / Female, 15.0ft (4.6m)	3	45.00	42.30	39.60	36.90	34.20
CTL3VGAMF-25T	Super Thin SVGA Cable, HD15 Male / Female, 25.0ft (7.6m)	3	60.00	56.40	52.80	49.20	45.60
CTL3VGAMF-50T	Super Thin SVGA Cable, HD15 Male / Female, 50.0ft (15.2m)	3	97.50	91.65	85.80	79.95	74.10

### ✓RoHS Plenum Jacket Super Thin SVGA Cables - HD15M to HD15M or HD15F

This series is identical to our Super Thin SVGA cables with one important exception, the cable outer jacket and HD15 connector backshell overmold are made from CMP grade plenum material. Color: Black.

CTL3VGAMM-5TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 5.0ft (1.5m)	3	80.00	78.40	76.80	75.20	73.60
CTL3VGAMM-10TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 10.0ft (3.0m)	3	130.00	127.40	124.80	122.20	119.60
CTL3VGAMM-15TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 15.0ft (4.6m)	3	180.00	176.40	172.80	169.20	165.60
CTL3VGAMM-25TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	280.00	274.40	268.80	263.20	257.60
CTL3VGAMM-50TP	Super Thin Plenum SVGA Cable, HD15 Male / Male, 50.0ft (15.2m)	3	530.00	519.40	508.80	498.20	487.60
CTL3VGAMF-5TP	Super Thin Plenum SVGA Cable, HD15 Male / Female, 5.0ft (1.5m)	3	80.00	78.40	76.80	75.20	73.60
CTL3VGAMF-10TP	Super Thin Plenum SVGA Cable, HD15 Male / Female, 10.0ft (3.0m)	3	130.00	127.40	124.80	122.20	119.60
CTL3VGAMF-15TP	Super Thin Plenum SVGA Cable, HD15 Male / Female, 15.0ft (4.6m)	3	180.00	176.40	172.80	169.20	165.60
CTL3VGAMF-25TP	Super Thin Plenum SVGA Cable, HD15 Male / Female, 25.0ft (7.6m)	3	280.00	274.40	268.80	263.20	257.60
CTL3VGAMF-50TP	Super Thin Plenum SVGA Cable, HD15 Male / Female, 50.0ft (15.2m)	3	530.00	519.40	508.80	498.20	487.60

### ✓RoHS LSZH Jacket Super Thin SVGA Cables – HD15M to HD15M or HD15F Cable Assembly

This series of SVGA cables features both our small diameter Super Thin cable and our LSZH jacket for applications where low smoke is critical. An additional feature of this series is our reversible hardware allowing both panel mount using standoffs or traditional thumbscrews. High quality video signal transmission is assured as a result of the three 75 Ohm coaxial lines used in these premium SVGA assemblies. The low profile configuration of our fully molded HD15 backshell makes these assemblies ideal for tight fit installations. Available in 5 standard lengths from 5 to 50 feet.

CTL3VGAMM-5TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 5.0ft (1.5m)	3	46.00	43.24	40.48	37.72	34.96
CTL3VGAMM-10TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 10.0ft (3.0m)	3	61.00	57.34	53.68	50.02	46.36
CTL3VGAMM-15TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 15.0ft (4.6m)	3	76.00	71.44	66.88	62.32	57.76
CTL3VGAMM-25TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 25.0ft (7.6m)	3	106.00	99.64	93.28	86.92	80.56
CTL3VGAMM-50TZ	Super Thin LSZH SVGA Cable, HD15 Male / Male, 50.0ft (15.2m)	3	181.00	170.14	159.28	148.42	137.56
CTL3VGAMF-5TZ	Super Thin LSZH SVGA Cable, HD15 Male / Female, 5.0ft (1.5m)	3	46.00	43.24	40.48	37.72	34.96
CTL3VGAMF-10TZ	Super Thin LSZH SVGA Cable, HD15 Male / Female, 10.0ft (3.0m)	3	61.00	57.34	53.68	50.02	46.36
CTL3VGAMF-15TZ	Super Thin LSZH SVGA Cable, HD15 Male / Female, 15.0ft (4.6m)	3	76.00	71.44	66.88	62.32	57.76
CTL3VGAMF-25TZ	Super Thin LSZH SVGA Cable, HD15 Male / Female, 25.0ft (7.6m)	3	106.00	99.64	93.28	86.92	80.56
CTL3VGAMF-50TZ	Super Thin LSZH SVGA Cable, HD15 Male / Female, 50.0ft (15.2m)	3	181.00	170.14	159.28	148.42	137.56

**Best Seller**

CTL3VGAMM-T

CTL3VGAMM-T

CTL3VGAMF-T

CTL3VGAMF-T

CTL3VGAMF-TP

CTL3VGAMM-TP

CTL3VGAMF-TP

CTL3VGAMF-TZ

CTL3VGAMM-TZ

CTL3VGAMF-TZ



### Free technical support

Call toll free at 1-800-343-1455

if you have questions about your application.