


Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>RoHS</b> RG59B/U - 75 Ohm Coaxial Cables with One Inline BNC to One Right Angle BNC Plug						
CC59B-1HR	RG59B Cable, BNC Male / 90° Male, 1.0ft (0.3m)	11.25	10.80	10.35	9.90	9.45
CC59B-1.5HR	RG59B Cable, BNC Male / 90° Male, 1.5ft (0.5m)	11.50	11.04	10.58	10.12	9.66
CC59B-2HR	RG59B Cable, BNC Male / 90° Male, 2.0ft (0.6m)	11.75	11.28	10.81	10.34	9.87
CC59B-3HR	RG59B Cable, BNC Male / 90° Male, 3.0ft (0.9m)	12.25	11.76	11.27	10.78	10.29
CC59B-4HR	RG59B Cable, BNC Male / 90° Male, 4.0ft (1.2m)	12.75	12.24	11.73	11.22	10.71
CC59B-5HR	RG59B Cable, BNC Male / 90° Male, 5.0ft (1.5m)	13.25	12.72	12.19	11.66	11.13
CC59B-7.5HR	RG59B Cable, BNC Male / 90° Male, 7.5ft (2.3m)	14.50	13.92	13.34	12.76	12.18
CC59B-10HR	RG59B Cable, BNC Male / 90° Male, 10.0ft (3.0m)	15.75	15.12	14.49	13.86	13.23

<b>RoHS</b> RG59B/U - 75 Ohm Coaxial Cables with Two Right Angle BNC Plugs						
CC59B-1HR2	RG59B Cable, BNC 90° Male / 90° Male, 1.0ft (0.3m)	15.00	14.40	13.80	13.20	12.60
CC59B-2HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.0ft (0.6m)	15.50	14.88	14.26	13.64	13.02
CC59B-2.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 2.5ft (0.8m)	15.75	15.12	14.49	13.86	13.23
CC59B-3HR2	RG59B Cable, BNC 90° Male / 90° Male, 3.0ft (0.9m)	16.00	15.36	14.72	14.08	13.44
CC59B-7.5HR2	RG59B Cable, BNC 90° Male / 90° Male, 7.5ft (2.3m)	18.25	17.52	16.79	16.06	15.33

**Thinline 75 Ohm (.11"/2.8mm Dia.) Coaxial Cable Assemblies**


Substitute our smaller diameter, more flexible, lighter weight thinline cable assemblies for your traditional 75 Ohm cable assemblies. This coaxial cable features a spiral tinned copper shield and a proprietary air foamed dielectric.

Thinline		<b>Thinline</b> <ul style="list-style-type: none"> <li>Center Conductor: 28 AWG (7 x 38) stranded tinned copper wire</li> <li>Shielding: Tinned copper spiral shield (95% coverage)</li> <li>Insulation: Foamed polyethylene</li> <li>Jacket: Black PVC</li> <li>Operating Temperature: -40°C - +80°C</li> </ul>	NOMINAL ATTENUATION		
			MHz	db/100ft	db/100m
			5	1.4	4.6
			10	2.1	6.9
			30	3.8	12.5
			50	5.1	16.7
			100	7.6	24.9

<b>RoHS</b> Thinline - 75 Ohm Coaxial Cables with Two Inline BNC Plugs						
CTL1B-1	Thinline Cable, BNC Male / Male, 1.0ft (0.3m)	7.00	6.72	6.44	6.16	5.88
CTL1B-2.5	Thinline Cable, BNC Male / Male, 2.5ft (0.8m)	7.75	7.44	7.13	6.82	6.51
CTL1B-5	Thinline Cable, BNC Male / Male, 5.0ft (1.5m)	9.00	8.64	8.28	7.92	7.56
CTL1B-7.5	Thinline Cable, BNC Male / Male, 7.5ft (2.3m)	10.25	9.84	9.43	9.02	8.61
CTL1B-10	Thinline Cable, BNC Male / Male, 10.0ft (3.0m)	11.50	11.04	10.58	10.12	9.66
CTL1B-15	Thinline Cable, BNC Male / Male, 15.0ft (4.6m)	14.00	13.44	12.88	12.32	11.76
CTL1B-25	Thinline Cable, BNC Male / Male, 25.0ft (7.6m)	19.00	18.24	17.48	16.72	15.96

**RG179B/U - High Temperature Cables with Inline BNC Plugs**


This 75 Ohm cable features a Brown tinted FEP outer jacket and an operating temperature of 200°C.

RG179B/U		<b>RG179B/U</b> <ul style="list-style-type: none"> <li>Center Conductor: 30 AWG (7 x 38) stranded silver plated copper covered steel</li> <li>Shielding: Silver coated copper braid (95% coverage)</li> <li>Insulation: TFE teflon</li> <li>Jacket: Brown FEP</li> <li>Operating Temperature: -70°C - +200°C</li> </ul>	NOMINAL ATTENUATION		
			MHz	db/100ft	db/100m
			50	8.5	27.9
			100	10.0	32.8
			200	12.5	41.0
			400	16.0	52.5
			1000	24.0	78.7

<b>RoHS</b> RG179B/U - 75 Ohm High Temperature Cable with Two Inline BNC Plugs						
CC179B-1	RG179 Cable, BNC Male / Male, 1.0ft (0.3m)	21.00	20.16	19.32	18.48	17.64
CC179B-1.5	RG179 Cable, BNC Male / Male, 1.5ft (0.5m)	21.75	20.88	20.01	19.14	18.27
CC179B-2	RG179 Cable, BNC Male / Male, 2.0ft (0.6m)	22.50	21.60	20.70	19.80	18.90
CC179B-2.5	RG179 Cable, BNC Male / Male, 2.5ft (0.8m)	23.25	22.32	21.39	20.46	19.53
CC179B-5	RG179 Cable, BNC Male / Male, 5.0ft (1.5m)	27.00	25.92	24.84	23.76	22.68
CC179B-7.5	RG179 Cable, BNC Male / Male, 7.5ft (2.3m)	30.75	29.52	28.29	27.06	25.83
CC179B-10	RG179 Cable, BNC Male / Male, 10.0ft (3.0m)	34.50	33.12	31.74	30.36	28.98
CC179B-15	RG179 Cable, BNC Male / Male, 15.0ft (4.6m)	42.00	40.32	38.64	36.96	35.28

**RG187/U - High Temperature 75 Ohm Cables with Inline BNC Plugs**

This series features a small diameter (.110/2.8mm) 75 Ohm cable with a 200°C operating temperature.

RG187/U		<b>RG187/U</b> <ul style="list-style-type: none"> <li>Center Conductor: 30 AWG (7 x 38) stranded silver plated copper covered steel</li> <li>Shielding: Silver coated copper braid (95% coverage)</li> <li>Insulation: TFE teflon</li> <li>Jacket: TFE teflon tape wrap</li> <li>Operating Temperature: -70°C - +200°C</li> </ul>	NOMINAL ATTENUATION		
			MHz	db/100ft	db/100m
			50	8.5	27.9
			100	10.0	32.8
			200	12.5	41.0
			400	16.0	52.5
			1000	24.0	78.7

**RG187/U - 75 Ohm Coaxial Cable High Temperature with Two Inline BNC Plugs**

CC187B-1	RG187 Cable, BNC Male / Male, 1.0ft (0.3m)	33.50	32.16	30.82	29.48	28.14
CC187B-1.5	RG187 Cable, BNC Male / Male, 1.5ft (0.5m)	35.00	33.60	32.20	30.80	29.40
CC187B-2	RG187 Cable, BNC Male / Male, 2.0ft (0.6m)	36.50	35.04	33.58	32.12	30.66
CC187B-2.5	RG187 Cable, BNC Male / Male, 2.5ft (0.8m)	38.00	36.48	34.96	33.44	31.92
CC187B-5	RG187 Cable, BNC Male / Male, 5.0ft (1.5m)	45.50	43.68	41.86	40.04	38.22
CC187B-7.5	RG187 Cable, BNC Male / Male, 7.5ft (2.3m)	53.00	50.88	48.76	46.64	44.52
CC187B-10	RG187 Cable, BNC Male / Male, 10.0ft (3.0m)	60.50	58.08	55.66	53.24	50.82
CC187B-15	RG187 Cable, BNC Male / Male, 15.0ft (4.6m)	75.50	72.48	69.46	66.44	63.42



**Technical resources**

Free tips, tutorials and downloads help you learn all about connectivity. Visit [L-com.com/Resources](http://L-com.com/Resources)